



Certificate of Conformity

LOVAG-Certificate No.: IT 18.038
Page 1 of 2

Apparatus Low-voltage assembly

415 V (U_n) – 690 V (U_i) – 8 kV (U_{imp}) – 50 Hz (f) – 3340 A (I_{nA}) – 50 kA (I_{cc}) – 50 kA (I_{cw}) x 1 s (t) – IP30

This Certificate applies only to the apparatus verified. The responsibility for conformity of any apparatus having the same designation with that verified rests with the manufacturer or responsible vendor.

This certificate has been prepared according to LOVAG (Low Voltage Agreement Group) Objectives and Operating Principles of mutual recognition. The responsible certification body as a member of LOVAG issues a Certificate of Conformity with the above mentioned Standard(s) following the exclusive use of LOVAG Verification instruction wherever applicable.

Only integral reproduction of this Certificate or reproductions of this page accompanied by any page(s) on which are stated the verifications performed and the assigned rated characteristics of the apparatus verified, are permitted without written permission from the LOVAG Signatory responsible for this Certificate



Designation Type XL³ S 4000 Arrangement 143 IP 30

Manufacturer Legrand SNC
128, Avenue du Marechal du Lattre de Tassigny
87045 Limoges Cedex - France

Applicant: Legrand SNC
128, Avenue du Marechal du Lattre de Tassigny
87045 Limoges Cedex - France

Verified by: ACAE Laboratory:
IB01 Varese (Italy)

The apparatus, constructed in accordance with the description mentioned in the Report listed in this Certificate has been subjected to the series of proving verifications in accordance with

IEC 61439-2 Ed.2.0 (2011-08) and EN 61439-2 (2011-10):

- 10.4 Clerances and creepage distances
- 10.9 Dielectric properties
- 10.10.2.3.5 Temperature rise

The results are shown in the Report in accordance to LOVAG. The values obtained and the general performance are considered to comply with the above Standard(s) and to justify the characteristics assigned by the manufacturer as stated at pages no. 2

Responsible Certification Body: ACAE
Via Tito Livio, 5 – 24123 – BERGAMO (Italy)



PRD N° 070B
Signatory of EA, IAF and ILAC
Mutual Recognition Agreements

Authorized Signature: Virginio Scarioni
Date: 2018.03.13



Certificate of Conformity

LOVAG-Certificate No.: IT 18.038
Page 2 of 2



Circuit	D1 Incomer	Main copper busbar	Vertical Alu busbar 2x F7436	Horiz. upper busbar	Vertical Alu busbar 2x F7437
Rated operational voltage (U_e) V	415	415	415	415	415
Rated insulation voltage (U_i) V	1000	1000	1000	1000	1000
Rated current (I_{nc}) A	3340	3340	2480	1260	1260
Rated diversity factor	1	1	1	1	1
Rated short-time withstand current (I_{cw}) kA – (t) s	50–1	50–1	50–1	50–1	50–1
Rated peak withstand current (I_{pk}) kA	105	105	105	105	105
Rated conditional short-circuit current (I_{cc}) kA	50	50	50	50	50

Circuit	D2	D3	D4	D5	D6	D7
Rated operational voltage (U_e) V	415	415	415	415	415	415
Rated insulation voltage (U_i) V	1000	1000	690	690	690	690
Rated current (I_{nc}) A	860	1220	450	480	210	120
Rated diversity factor	1	1	1	1	1	1
Rated short-time withstand current (I_{cw}) kA – (t) s	-	-	-	-	-	-
Rated peak withstand current (I_{pk}) kA	-	-	-	-	-	-
Rated conditional short-circuit current (I_{cc}) kA	50	50	50	50	50	50

This document includes: Test Report No. 1318
Issue date: 2018.02.27



PRD N°070B
Signatory of EA, IAF and ILAC
Mutual Recognition Agreements

Responsible Certification Body: ACAE
Via Tito Livio, 5 – 24123 – BERGAMO (Italy)

Authorized Signature: Virginio Scarioni

Date: 2018.03.13