

LICENCE

No. 22486 replaces No.21505

Issued to:
Applicant:
Legrand Group Belgium N.V.
Hector Henneaulaan 366
1930 Zaventem
Belgium

Licensee:
Legrand Group Belgium N.V.
Hector Henneaulaan 366
1930 Zaventem
Belgium



Product : rocker/push-button switches (for fixed installations)
Trade name(s) : LEGRAND
Type(s)/model(s) : Series VALENA NEXT (See appendix)

The product and any acceptable variation thereto is specified in the annex to this licence and the documents therein referred to.

SGS CEBEC hereby declares that the above-mentioned product has been certified on the basis of:


- a type test according to the standard specified in annex
- an inspection of the production location
- a certification agreement with the number 178

SGS CEBEC hereby grants the right to use the CEBEC certification mark
The CEBEC certification mark may be applied to the product as specified in this licence for the duration of the CEBEC certification agreement and under the conditions of the CEBEC certification agreement.

This licence is issued on : 14/03/2022

ir. C. Lana,
Certification Manager

© Only integral publication of this certificate, including the annex, is allowed
This certificate is only valid combined with the publication on the following web address: www.sgs.com/ee



SPECIFICATION OF THE CERTIFIED PRODUCT

Product data

Product	:	rocker/push-button switches (for fixed installations)
Trade name(s)	:	LEGRAND
Type(s)/Model(s)	:	Series VALENA NEXT (See appendix)
rated current (In)	:	6A, 6AX, 10AX
rated voltage (Un)	:	250 V
nature of supply	:	AC
pattern no(s).	:	2x6, 6+6, 1, 6, 7
method of actuating	:	rocker, rocker with momentary contact, cord-operated, cord-operated momentary
contact opening (gap)	:	normal gap, mini-gap
protection against harmful ingress of water	:	Ip20
type of terminals	:	screw type, screwless type
protection against electric shock	:	enclosed
method of mounting	:	flush type
method of installation	:	design A
certification mark	:	complies with the requirements
markings	:	are shown on the body

Additional information

See Appendix

TESTS

Test requirements

NBN EN 60669-1 based on EN 60669-1:2018 + AC:2018-11

Test results

The test results are laid down in certification file ref.632608/01

Remarks


This certificate is based on certificate ref. CB FR_705135/A1 and test reports ref. 158728-730555A, 58728-730555B, 154566-718845B, 150730-709904B, 130899-663536Cr2016-10-05, 136898-675824A, 132235-666597A, 102524-603915 and 173730-769190

Conclusion

The examination proved that all certification requirements were met.

Reviewed by, project leader : Luigi Zanutto - 14/03/2022

Certification Manager :



2022-03-14

FACTORY LOCATION(S)

Envera Empleo, SLU
C/Traspaderne, 9
28042 Madrid
Spain

Legrand France
128, avenue du Maréchal de Lattre de Tassigny
87045 LIMOGES CEDEX
France

Legrand ZRt.
IPartelep. út 14
6600 SZENTES
Hungary

References : Series VALENA NEXT

Switches

Reference (white)	Reference (Aluminium)	Reference (Dark)	Pattern Nbr.	Actuating	Terminals	Rated current / Rated voltage	Specificity
7 415 42	7 416 42	7 417 42	2x6	Rocker	Screwless	10AX/250V	
7 415 51	7 416 51	7 417 51	6+6	Rocker+Push-button	Screwless	10AX/250V+6A/250V	
7 415 54	7 416 54	7 417 54	1	Rocker	Screwless	10AX/250V	
7 415 40	7 416 40	7 417 40	6	Rocker	Screwless	10AX/250V	
7 415 41	7 416 41	7 417 41	6	Rocker	Screwless	10AX/250V	Pilot light
7 415 49	7 416 49	7 417 49	2x6	Push-button	Screwless	6A/250V	
7 415 47	7 416 47	7 417 47	6	Push-button	Screwless	6A/250V	
7 415 48	7 416 48	7 417 48	6	Push-button	Screwless	6A/250V	Pilot light
7 415 50	7 416 50	7 417 50	6	Push-button	Screwless	6A/250V	Label holder
7 415 45	7 416 45	7 417 45	7	Rocker	Screw-type	10AX/250V	
7 415 46	7 416 46	7 417 46	6	Rocker Cord operated	Screwless	6AX/250V	
7 415 52	7 416 52	7 417 52	6	Push-button cord operated	Screwless	6A/250V	
7 415 57	7 416 57	7 417 57	6	Push-button	Screwless	6A/250V	
7 415 59	7 416 59	7 417 59	6	Rocker	Screwless	6AX/250V	
7 415 80	7 416 80	7 417 80	N/A	N/A	N/A	N/A	Obturator

Cover plates

	White	White Chrome	White/Rose	Aluminium	Aluminium Chrome	Dark	Dark Chrome	Dark Copper
1 gang	7 411 01	7 411 11	7 411 21	7 411 31	7 411 41	7 411 51	7 411 61	7 411 71
2 gang	7 411 02	7 411 12	7 411 21	7 411 32	7 411 01	7 411 52	7 411 62	7 411 72
3 gang	7 411 03	7 411 13	7 411 21	7 411 33	7 411 01	7 411 53	7 411 63	7 411 73
4 gang	7 411 04	7 411 14	7 411 21	7 411 34	7 411 01	7 411 54	7 411 64	7 411 74
5 gang	7 411 05	7 411 15	7 411 21	7 411 35	7 411 01	7 411 55	7 411 65	7 411 75
2 gang spacing 57	7 411 08	7 411 18	7 411 21	7 411 38	7 411 01	7 411 58	7 411 68	7 411 78
3 gang spacing 57	7 411 09	7 411 19	7 411 21	7 411 39	7 411 01	7 411 59	7 411 69	7 411 79