

AENOR

Confía

ENEC Certification Body registered under ID # 01. For further information, please consult www.enec.com

LICENCE

to use the European Mark



Licence Nr. ENEC/001218

Under the conditions given in the following pages of this document, the licence to use the ENEC Mark in conjunction with the suffix 01, as shown above, has been issued to:

LEGRAND GROUP ESPAÑA, S.L.
HIERRO, 56
28850 TORREJON DE ARDOZ (Madrid – España / Spain)

For the product(s):

LED luminaires for emergency lighting

Trade name(s):

LEGRAND

Complying with the following European Standards:

EN IEC 60598-1:2021;
EN 60598-2-22:2014; EN 60598-2-22:2014/A1:2020;
EN 62262:2002

Date: 2023-04-10

Signature:

A handwritten signature in blue ink, appearing to read 'Rafael García', written over a horizontal line.

Name: Rafael García
Position: Chief Executive Officer

This licence has been issued under the presumption and conditional on the fact that the licensee holds all necessary legal rights with regard to the product presented for testing and certification.

AENOR INTERNACIONAL, S.A.U.
Cl Génova, 6
28004 MADRID (Spain)

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type of Product	LED LUMINAIRES FOR EMERGENCY LIGHTING
r1) Certificate n°	ENEC/001218
r2) Date of the Certificate	2023-04-10
r3) report n°	2022010001B1-M2
r4) Name and address of the licensee	LEGRAND GROUP ESPAÑA, S.L. HIERRO, 56 28850 TORREJON DE ARDOZ (Madrid - España / Spain)
r5) Address of the factory	HIERRO, 56 28850 TORREJON DE ARDOZ (Madrid - España / Spain)
r6) European Standard	EN IEC 60598-1:2021; EN 60598-2-22:2014; EN 60598-2-22:2014/A1:2020; EN 62262:2002
r7) Type reference	See above for details
r8) Trade Mark	LEGRAND
r9) Rated voltage and frequency	230 V~; 50/60 Hz
r10) N° lamps x rated power, type and lampholder	See above for details
r11) IP degree of protection	IP42; IK 07
r12) Power supply connection means	Bornes Terminals
r13) Classif. per holding surface material	Apta para superficies normalmente inflamables Suitable for normally flammable surfaces
r14) Protection against electric shocks (class)	Clase II Class II
r15) Rated lumen output and duration	See above for details
r16) Battery features	See above for details
r17) Additional information	See above for details
r18) General data	See above for details
Date of expiry: 2026-06-30	This certificate supersedes certificate 007/001218, dated 2023-01-05.

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Nº lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
660032	2 x 0,25W; módulo module LED	100 lm - 1h	NiCd 3,6 V 0,7 Ah	No permanente Non maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X- LIGHT 360 (STD)
660042	4 x 0,25W; módulo module LED	100 lm - 1h	NiCd 3,6 V 0,7 Ah	No permanente/Perm anente Non maintained/Maint ained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X- LIGHT 360 (STD)
660044	4 x 0,25W; módulo module LED	200 lm - 1h	NiCd 3,6 V 1,1 Ah	No permanente/Perm anente Non maintained/Maint ained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X- LIGHT 360 (STD)
660045	8 x 0,25W; módulo module LED	350 lm - 1h	NiMH 3,6 V 1,5 Ah	No permanente/Perm anente Non maintained/Maint ained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X- LIGHT 360 (STD)
660047	6 x 0,25W; módulo module LED	200 lm - 2h	NiMH 3,6 V 1,5 Ah	No permanente/Perm anente Non maintained/Maint ained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X- LIGHT 360 (STD)

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Nº lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
660048	4 x 0,25W; módulo module LED	100 lm - 3h	NiCd 3,6 V 1,1 Ah	No permanente/Permanente Non maintained/Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; U22 ROND / X-LIGHT 360 (STD)
660142	4 x 0,25W; módulo module LED	100 lm - 1h	NiMH 3,6 V 0,5 Ah	No permanente/Permanente Non maintained/Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X-LIGHT 360 (Autotest)
660144	6 x 0,25W; módulo module LED	200 lm - 1h	NiMH 3,6 V 1,1 Ah	No permanente/Permanente Non maintained/Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X-LIGHT 360 (Autotest)
660145	8 x 0,25W; módulo module LED	350 lm - 1h	NiMH 3,6 V 1,5 Ah	No permanente/Permanente Non maintained/Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X-LIGHT 360 (Autotest)
660146	4 x 0,25W; módulo module LED	100 lm - 3h	NiMH 3,6 V 1,1 Ah	No permanente/Permanente Non maintained/Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; U22 ROND / X-LIGHT 360 (Autotest)

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Nº lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
660147	6 x 0,25W; módulo module LED	200 lm - 2h	NiMH 3,6 V 1,5 Ah	No permanente/Permanente Non maintained/Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X-LIGHT 360 (Autotest)