

**IEC****IECEE**

®

TM

Ref. Certif. No.

**FR\_720352**

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

**CB TEST CERTIFICATE**

Product

**Socket-outlet for fixed-electrical installations**

Name and address of the applicant

**LEGRAND FRANCE**  
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY  
87045 LIMOGES CEDEX  
FRANCE

Name and address of the manufacturer

**LEGRAND FRANCE**  
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY  
87045 LIMOGES CEDEX  
FRANCE

Name and address of the factory

**LEGRAND FRANCE**  
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY  
87045 LIMOGES CEDEX  
FRANCE

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

PLEXO series / 0 697 85L, 0 698 85L

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR\_716555/A1 dated 09/03/2023. Update further to the evolution of the standard(s)

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022

As shown in the Test Report Ref. No. which forms part of this Certificate

21918853-799723

This CB Test Certificate is issued by the National Certification Body

**LCIE**LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE  
33 avenue du Général Leclerc  
92260 Fontenay-aux-Roses, FRANCE[www.lcie.fr](http://www.lcie.fr)LABORATOIRE CENTRAL DES  
INDUSTRIES ELECTRIQUES

S.A.S au capital de 15.745.984 €

RCS Nanterre B 408 363 174

33 avenue du Général Leclerc

F - 92266 FONTENAY AUX ROSES

Signature: **Julien GAUTHIER**  
Certification Officer

Date: 04/11/2024

## ANNEX

### References, ratings and main characteristics:

#### MECHANISMS

Type Reference	References Anthracite	Function	Characteristics	Type of Terminals	IP	Mounting	Specificities
EVFV1	0 697 85L	2P+T	16A 250V~	Screw-type (rigid and flexible)	IP55	Surface-type	mechanism with box
EVFV1	0 698 85L	2P+T	16A 250V~	Screw-type (rigid and flexible)	IP55	/	mechanism only

#### ACCESSORIES

References Anthracite	Designation
0 696 01L	box 1 gang with membrane cable gland
0 700 56	box 1 gang with membrane cable gland
0 696 06L	frame 1 gang
0 694 94L	peg fixation


#### CLASSIFICATION

standard Sheet:	I (NF C 61-314) / V (CEE7)
rated current (A)	16A
rated voltage (V)	250V~
degree of protection	IP55
provision for earthing	with earthing contact
method of connecting the cable	Rewirable
type of terminals	Screw-type
colour	Grey
<b>Pins</b>	Not solid
degree of protection against electric shock	Increased protection
existence of shutters	With shutters
method of application - mounting	Surface-type or Flush-type
method of installation	Design A



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE  
 33 avenue du Général Leclerc  
 92260 Fontenay-aux-Roses, FRANCE  
[www.lcie.fr](http://www.lcie.fr)

Date: 04/11/2024



Signature: **Julien GAUTHIER**  
 Certification Officer