

IEC

IECEE

Ref. Certif. No.

FR_716141

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Luminaire for emergency lighting
Self-contained luminaires for emergency lighting

Name and address of the applicant

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the factory

LEGRAND FRANCE
1 RUE HENRI FREYSSINET
17140 LAGORD
FRANCE

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See annex

Trademark / Brand (if any)

legrand

Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

Range B66
6 625 10, 6 625 15 : NM

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_701851 dated 01/12/2017. Update the list of product references, Update further to the evolution of the standard(s)

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60598-1:2014+A1:2017
IEC 60598-2-22:2014+A1:2017


As shown in the Test Report Ref. No. which forms part of this Certificate

173002-766667-A Version : 01

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr



Signature: Jérôme REYSSON
Certification Officer

Date: 15/12/2022

ANNEX

Ratings and main characteristics:

Caractéristiques / Characteristics	Valeurs / Values
Type / Type	NM
Tension assignée / Rated voltage	230V~
Nature du courant / Nature of supply	AC
Fréquence assignée / Rated frequency	50/60 Hz
Puissance assignée / Rated power	/
Classe de protection contre les chocs électriques / Class of protection from electric shock	II
Degré IP / IP degree	66
Degré IK / IK degree	08
Flux assigné / Rated lumen output	6 625 10 : 250 lm à 1h 6 625 15 : 350 lm à 1h
Nature accumulateur (Type, Nombre, Tension, Capacité) / Battery type	6 625 10 Ni-Cd [(4 x 1,2 / 1,5 Ah) + (2 x 1,2 / 1,5 Ah)] BYD SC1500mAh Ni-Cd [(4 x 1,2 / 1,6 Ah) + (2 x 1,2 / 1,6 Ah)] ARTS ENERGY VNT Cs U 6 625 15 Ni-Cd [2 x (4 x 1,2 V) / 1,5Ah] BYD SC1500mAh Ni-Cd [2 x (4 x 1,2 V) / 1,6Ah] ARTS ENERGY VNT Cs U
Source lumineuse - Etat de fonctionnement de secours (lampes de secours) - Type, nombre / Light source - Emergency mode (emergency lamps) - Type, number	6 625 10 : 1 tube x 8 W 6 625 15 : 1 tube x 8 W



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 15/12/2022


 Signature: Jérôme REYSSON
Certification Officer