

**IEC****IECEE**

Ref. Certif. No.

**FR\_706411/M1**

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

**CB TEST CERTIFICATE**

Product

**Fixed switched socket-outlet**

Switched socket-outlets for fixed installations

Name and address of the applicant

**LEGRAND MAGYARORSZAG VILLAMOSSAGI RENDSZEREK ZRt**IPARTELEPI UT 14 PF 10  
6600 SZENTES- HUNGARY

Name and address of the manufacturer

**LEGRAND FRANCE**128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY  
87045 LIMOGES CEDEX- FRANCE

Name and address of the factory

**LEGRAND MAGYARORSZAG VILLAMOSSAGI RENDSZEREK ZRt**IPARTELEPI UT 14 PF 10  
6600 SZENTES - HUNGARY

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR\_706411 dated 22/07/2019. Change the name and address of manufacturer

 Additional Information on page 2


A sample of the product was tested and found to be in conformity with

IEC 60884-2-3:2006  
IEC 60884-1:2002(ed.3) +A1:2006 +A2:2013

As shown in the Test Report Ref. No. which forms part of this Certificate

ARFH-ESH-P22101318  
ARFH-19MY0492ACSHP

This CB Test Certificate is issued by the National Certification Body

**LCIE**LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE  
33 avenue du Général Leclerc  
92260 Fontenay-aux-Roses, FRANCE[www.lcie.fr](http://www.lcie.fr)LABORATOIRE CENTRAL DES  
INDUSTRIES ELECTRIQUES  
S.A.S au capital de 15.745.984 €  
RCS Nanterre B 408 363 174  
33 avenue du Général Leclerc  
F - 92266 FONTENAY AUX ROSESSignature:   
**Julien GAUTHIER**  
Certification Officer

Date: 15/12/2022

## ANNEX

### References, ratings and main characteristics:

Reference	Range*	Description	Color of enclosure	with cover plate	with support frame
572130	ARTEOR	2P+E 13A British Standard Single Pole switched 1 gang	White	575070	576002
572630	ARTEOR	2P+E 13A British Standard Single Pole switched 1 gang	Magnesium cover with black cover plate	575072	576002
570044	ARTEOR	2P+E 13A British Standard Single Pole switched 1 gang	Champagne cover with black cover plate	575072	576002
571044	ARTEOR	2P+E 13A British Standard Single Pole switched 1 gang	Alu cover with black cover plate	575072	576002


\* The "range" denotes applicant's categorization.

standard Sheet:	standard sheet of BS 1363-2
rated current (A)	13A
rated voltage (V)	250V
degree of protection	IP20
provision for earthing	with earthing contact
method of connecting the cable	rewirable
type of terminals	screw-type
colour	White, Magnesium, Champagne, Alu, Red, Green, Orange
<b>socket-outlets</b>	
multiple socket-outlets	
number of socket-outlets	13A : 1
degree of protection against electric shock	normal protection
existence of shutters	with shutters
method of application - mounting	flush-type
method of installation	design A
Intended for circuits where	a single earthing circuit provides protective earthing
<b>Switched socket-outlets without interlock</b>	
According to the method of actuating the switch	rocker
According to the switching of the neutral	unswitched neutral



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE  
 33 avenue du Général Leclerc  
 92260 Fontenay-aux-Roses, FRANCE

[www.lcie.fr](http://www.lcie.fr)



Signature: **Julien GAUTHIER**  
 Certification Officer

Date: 15/12/2022