



Product Service

Attestation of Conformity

No. T8A 111552 0010 Rev. 01**Holder of Attestation: Legrand Intelligent Electrical
(Huizhou) Co., Ltd.**

Bldg. B1-B3, East No.39 Hechang 6th Rd.
HZZK Hi-tech Industrial Development Zone
516007 Huizhou, Guangdong
PEOPLE'S REPUBLIC OF CHINA

**Product: Switches
(WIRELESS SWITCH 3GANG M SENSES
WHITE)**

This Attestation of Conformity is issued on a voluntary basis in support of the Conformity Assessment Module A of Radio Equipment Directive 2014/53/EU. On the basis of the referenced test reports, the samples of the listed product were found to comply with the essential requirements of the above mentioned directive as implemented in the standards used valid at the time the tests were carried out. For the requirements of the Article(s) 3(2) and 3(3) only harmonized standards valid at the moment of issuing where used. The used standards cover the essential requirements of the Radio Equipment Directive as applicable to this product. The manufacturer must ensure compliance of the manufactured products with the technical documentation and other requirements of the Radio Equipment Directive that apply to them. National legal requirements have to be considered before bringing the product to the market. For details see: www.tuvsud.com/ps-cert

Test report no.: 6891221002602**Date,** 2024-11-15

(Jessie He)

Page 1 of 2

This Attestation does not replace the regulatory EU Declaration of Conformity (DoC) and does not allow for CE marking. After preparation of the necessary documentation and establishing compliance to requirements of all applicable directives, the manufacturer may sign a DoC and apply the CE marking. The DoC is issued under the sole responsibility of the manufacturer.



Product Service

Attestation of Conformity

No. T8A 111552 0010 Rev. 01

Model(s): 281514MW, 281514MB, 281514DS, 574671, 574672, 574673, 574674, ZLE46, AA5203MB, AA5203MT, AA5203MW, AC5203MB, AC5203MT, AC5203MW

Trade name: legrand



Parameters:

Rated Voltage: 3VDC (power by CR2032 coin cell battery)

Test Report No.:

6871421002802 [EN 301 489-1, EN 301 489-17]

6891221002602 [EN 300 328, EN 62479, EN 50663]

6821021124203 [EN 62368-1]

**Tested
according to:**

EN 301 489-1 V2.2.3:2019

EN 301 489-17 V3.2.4:2020

EN 300 328 V2.2.2:2019

EN 62479:2010

EN 50663:2017

EN 62368-1:2014/A11:2017