



Ref. Certif. No.

SE-115438

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Rotary dimmer (Rotary dimmer RLC + LED)
Name and address of the applicant	Legrand Intelligent Electrical (Huizhou) Co., Ltd. Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, China
Name and address of the manufacturer	LEGRAND FRANCE 128, Avenue du Maréchal de Lattre de Tassigny, Limoges Cedex 87045, France
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See page 2
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	-
Model / Type Ref.	See page 2
Additional information (if necessary may also be reported on page 2)	<input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60669-1:2017 IEC 60669-2-1:2021
As shown in the Test Report Ref. No. which forms part of this Certificate	240920050GZU-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamnsgatan 43
Box 1103
SE-164 22 Kista, Sweden

Date: 11 December, 2024

intertek

Signature:
Anneli Averland Johansson



Ref. Certif. No.

SE-115438

Factories

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou,
Guangdong, China

Novateur Electrical & Digital Systems Private Limited
61/62, 6th Floor, Kalpataru Square, Kondivita Road, Anndheri (East), Mumbai-400059, Maharashtra, India

Legrand Electric LTD
Unit 12 No. 1 Industrial Estate, Medomsley Road, Consett County Durham DH8 6SR, United Kingdom

Ratings and principal characteristics

100-240 V, 50/60 Hz, Without contact gap, Integral type, IP20

1) At 100-200 V rating voltage:

5-150 W for incandescent lamp

5-150 VA for fluorescent Lamp: electronic step-down converter for extra low-voltage incandescent lamps
(for example, halogen), Iron core transformer for extra low-voltage incandescent lamps
(for example, halogen)

5-37 VA for self-ballasted fluorescent compact lamp (CFL) or self-ballast LED lamp

2) At 200-240 V rating voltage:

5-300 W for incandescent lamp;

5-300 VA for fluorescent Lamp; electronic step-down converter for extra low-voltage incandescent lamps
(for example, halogen), Iron core transformer for extra low-voltage incandescent lamps
(for example, halogen)

5-75 VA for self-ballasted fluorescent compact lamp (CFL) or self-ballast LED lamp

Model / Type Ref.

CXM17, AG05476AA, AG06488AA, 617635, 617735, 617835, 282419, 282419-C1, 282419-C2, 282419-C3,
282419-C, 833151, 832151, 731151, 832141, 832351, 832551, 833351, 833551, 281086MW, 281086MG,
281086MB, 281086DS, 281086CH, 281086DB, 281086BA, 281086BB, 281086BC, 281086MWSG,
281086MBSG, 281086DSSG, 281086CHSG, 281086DBSG, 281086BASG, 281086BBSG, 618035, 838103,
RW4415, RG4415, RA4415, JW4415, JG4415, JB4415, JW4415AB, 910641X, 912642X

Date: 11 December, 2024

Signature: