



Ref. Certif. No.

**ES2725-AENOR**

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**

**CB TEST CERTIFICATE**

Product

LED LUMINAIRES FOR EMERGENCY LIGHTING

Name and address of the applicant

LEGRAND GROUP ESPAÑA, S.L.  
HIERRO, 56  
28850 TORREJON DE ARDOZ (Madrid - Spain)

Name and address of the manufacturer

LEGRAND FRANCE LAGORD  
ZA DES GREFFIÈRES; 1, RUE EUGÈNE FREYSSINET  
F17140 LAGORD (France)

Name and address of the factory

SAME AS ABOVE

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

SEE ANNEX

Trademark (if any)

LEGRAND

Customer's Testing Facility (CTF) Stage used

---

Model / Type Ref.

SEE ANNEX

Additional information (if necessary may also be reported on page 2)

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60598-1:2020  
IEC 60598-2-22:2021  
IEC 62262:2002  
IEC 62262:2002/AMD1:2021

As shown in the Test Report Ref. No. which forms part of this Certificate

2023100536B1

This CB Test Certificate is issued by the National Certification Body

AENOR CONFÍA, S.A.U.  
CI Génova, 6  
ES-28004 MADRID (SPAIN)

Date: 2024-10-04

Signature:   
Rafael GARCÍA MEIRO  
CEO

# ANNEX TO CB CERTIFICATE N° ES2725-AENOR

## CERTIFIED REFERENCES AND THEIR PRINCIPAL CHARACTERISTICS

### LED LUMINAIRES FOR EMERGENCY LIGHTING

Type reference	Trade Mark	Rated voltage and frequency	N° lamps x rated power, type and lampholder	IP degree of protection	Power supply connection means	Classif. per holding surface material	Protection against electric shocks (class)	Rated lumen output and duration	Battery features	Additional information	General data
660460	LEGRAND	230 V~; 50/60 Hz	2 x 2 W	IP65, IK07	Bornes Terminals	Apta para superficies normalmente inflamables Suitable for normally flammable surfaces	Clase II Class II	1000 lm - 1h	LiFePO4 9,6 V - 3,2 Ah	No permanente Non maintained; Puesta en reposo remota Remote rest	Familia Series BAP; Autotest
660462	LEGRAND	230 V~; 50/60 Hz	3 x 2 W	IP65, IK07	Bornes Terminals	Apta para superficies normalmente inflamables Suitable for normally flammable surfaces	Clase II Class II	1500 lm - 1h	LiFePO4 9,6 V - 3,2 Ah	No permanente Non maintained; Puesta en reposo remota Remote rest	Familia Series BAP; Autotest
660463	LEGRAND	230 V~; 50/60 Hz	3 x 2 W	IP65, IK07	Bornes Terminals	Apta para superficies normalmente inflamables Suitable for normally flammable surfaces	Clase II Class II	2500 lm - 1h	LiFePO4 9,6 V - 3,2 Ah	No permanente Non maintained; Puesta en reposo remota Remote rest	Familia Series BAP; Autotest
660465	LEGRAND	230 V~; 50/60 Hz	3 x 2 W	IP65, IK07	Bornes Terminals	Apta para superficies normalmente inflamables Suitable for normally flammable surfaces	Clase II Class II	1500 lm - 2h	LiFePO4 9,6 V - 3,2 Ah	No permanente Non maintained; Puesta en reposo remota Remote rest	Familia Series BAP; Autotest
661460	LEGRAND	230 V~; 50/60 Hz	2 x 2 W	IP65, IK07	Bornes Terminals	Apta para superficies normalmente inflamables Suitable for normally flammable surfaces	Clase II Class II	1000 lm - 1h	LiFePO4 9,6 V - 3,2 Ah	No permanente Non maintained; Puesta en reposo remota Remote rest	Familia Series BAP; STD
661462	LEGRAND	230 V~; 50/60 Hz	3 x 2 W	IP65, IK07	Bornes Terminals	Apta para superficies normalmente inflamables Suitable for normally flammable surfaces	Clase II Class II	1500 lm - 1h	LiFePO4 9,6 V - 3,2 Ah	No permanente Non maintained; Puesta en reposo remota Remote rest	Familia Series BAP; STD
661463	LEGRAND	230 V~; 50/60 Hz	3 x 2 W	IP65, IK07	Bornes Terminals	Apta para superficies normalmente inflamables Suitable for normally flammable surfaces	Clase II Class II	2500 lm - 1h	LiFePO4 9,6 V - 3,2 Ah	No permanente Non maintained; Puesta en reposo remota Remote rest	Familia Series BAP; STD
662463	LEGRAND	230 V~; 50/60 Hz	3 x 2 W	IP65, IK07	Bornes Terminals	Apta para superficies normalmente inflamables Suitable for normally flammable surfaces	Clase II Class II	2500 lm - 1h	LiFePO4 9,6 V - 3,2 Ah	No permanente Non maintained; Puesta en reposo remota Remote rest	Familia Series BAP; STD