

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switches

Name and address of the applicant

LEGRAND Magyarország Villamossági Rendszerek ZRt.
Ipartelepí út 14.
6600 Szentés
Hungary

Name and address of the manufacturer

LEGRAND Magyarország Villamossági Rendszerek ZRt.
Ipartelepí út 14.
6600 Szentés
Hungary

Name and address of the factory

Note: When more than one factory, please report on page 2

LEGRAND Magyarország Villamossági Rendszerek ZRt.
Ipartelepí út 14.
6600 Szentés
Hungary

Ratings and principal characteristics

For new design (SEANO) types:
250 V~, 6 A or 10 A or 10 AX

Trademark / Brand (if any)

legrand

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

SU004, SU004N, SU005, SU003, BI10V1, PE10V2, SU007P,
SU008P, CO26P, SU005P with "SEANO" design
For detailed type differences and designation
see page 2 and page 3 of this CB Test Certificate.
For available accessories see CB Test Report.

Additional information (if necessary may also be reported on page 2)

See additional page(s) for further Additional information.
This CB Test Certificate is modification No.1 for
HU-004323, dated 2023-03-16 and it is issued due to
additional new design: "SEANO".
In this CB Test Certificate only the new added types
and their ratings have been listed.

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2002+A1+A2

As shown in the Test Report Ref. No. which forms part of this Certificate

HU215VBB 002

This CB Test Certificate is issued by the National Certification Body



TÜV Rheinland InterCert Kft., MEEI Division
H-1143 Budapest, Gizella út 51-57., Hungary
Web: www.tuv.com

Date: 2023-03-20

Signature:



Tötös Tamás László

Additional information :

Type differences and designation:

Type reference: SU004 (with "SEANO" design)
Designation: two-way switch (mechanism only)
Type of term.: screwless
Ref. no.: 7 650 06
Rated current: 10 AX

Type reference: SU004N (with "SEANO" design)
Designation: two-way switch (mechanism only)
Type of term.: screwless plus neutral
Ref. no.: 7 650 10
Rated current: 10 AX

Type reference: SU005 (with "SEANO" design)
Designation: two-way two gang switch (mechanism only)
Type of term.: screwless
Ref. no.: 7 650 08
Rated current: 10 AX

Type reference: SU003 (with "SEANO" design)
Designation: one-way two gang switch (mechanism only)
Type of term.: screwless
Ref. no.: 7 650 05
Rated current: 10 AX

Type reference: BI10V1 (with "SEANO" design)
Designation: two-pole switch (mechanism only)
Type of term.: with screw
Ref. no.: 7 650 02
Rated current: 10 AX

Type reference: PE10V2 (with "SEANO" design)
Designation: intermediate (mechanism only)
Type of term.: with screw
Ref. no.: 7 650 07
Rated current: 10 AX

Type reference: SU007P (with "SEANO" design)
Designation: two-way push-button switch (mechanism only)
Type of term.: screwless
Ref. no.: 7 650 11
Rated current: 10 A

Type reference: SU008P (with "SEANO" design)
Designation: two-way push button switch (mechanism only)
Type of term.: screwless plus neutral
Ref. no.: 7 650 17
Rated current: 10 A

Additional information :

Type reference: CO26P (with "SEANO" design)
Designation: pull-cord changeover pushbutton switch (white)
Type of term.: screwless
Ref. no.: 7 651 18
Rated current: 6 A

Type reference: SU005P (with "SEANO" design)
Designation: two-way two gang push-button switch (mechanism only)
Type of term.: screwless
Ref. no.: 7 650 18
Rated current: 10 A



Date: 2023-03-20

Signature:


Tötös Tamás László