

IEC**IECEE**

®

™

Ref. Certif. No.

FR_719272**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME****CB TEST CERTIFICATE**

Product

Electronic switch

Name and address of the applicant

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the factory

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

Series : PLEXO
References : See Annex

Additional information (if necessary may also be reported on page 2)

/
 Additional Information on page 2


A sample of the product was tested and found to be in conformity with

IEC 60669-1:2017
IEC 60669-2-1:2021

As shown in the Test Report Ref. No. which forms part of this Certificate

18093057-787011

This CB Test Certificate is issued by the National Certification Body

**LCIE**LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCEwww.lcie.frLABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES

S.A.S au capital de 15.745.984 €

RCS Nanterre B 408 363 174

33 avenue du Général Leclerc

F - 92266 FONTENAY AUX ROSES

Signature:
Julien GAUTHIER
Certification Officer

Date: 12/06/2024



Ref. Certif. No.

FR_719272

ANNEX

Mechanisms

Trademark	Type Reference	References Series / Colour 1	Pattern	Characteristics	Type of Terminals	IK	Mounting
Legrand	CXG35	0 695 17L	1	230V~ 50-60Hz	Screw type (rigid and flexible)	IK08	See Table

Classification

Function / Patern number	1
Contact opening (gap)	Micro-gap
Degree of protection	IP55
Method of actuating	Optical
Method of mounting	Flush type / Surface Type
Method of installation	Design A
Type of terminals	Screw type (rigid and flexible)
Rated current (A) / Power (VA/W)	1400 W
Rated voltage (V)	230V~
Load	1400 W Halogen lamps
	200 VA LED
	500 VA Fluorescent compact lamps
	500 VA Feromagnetic transformers for ELV halogen lamps
	500 VA Electronic transformers for ELV halogen lamps

Accessories

References White	References Grey	References Anthracite	References Sable	References	Designation / Function
0 696 89L	0 696 51L	0 696 01L	0 698 63L	-	Box 1 gang with membrane cable gland
0 696 92L	0 696 81L	0 696 06L	0 698 90L	-	Frame 1 gang



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr



Signature: **Julien GAUTHIER**
Certification Officer

Date: 12/06/2024