



Ref. Certif. No.

FR_711660/M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Shaver transformers and shaver supply units

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, Huizhou, 516001
Guangdong - CHINA

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, Huizhou, 516001
Guangdong - CHINA

Note: When more than one factory, please report on page 2

☐ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)

legrand

Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

Series: MALLIA
References: See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_711660 dated 09/06/2021.
Change of licence holder and trademark
Addition of components

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 61558-1:2005 +A1:2009(ed.2)
IEC 61558-2-5:2010(ed. 2)

As shown in the Test Report Ref. No. which forms part of this Certificate

ARLI-ESH-P24110873

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 11/06/2025

Signature:



ANNEX

References, ratings and main characteristics:

Model list:

Reference	Rated voltage		Color of enclosure
	Supply	Output	
2 811 35	230V	120/230V	White complete
2 811 35MW	230V	120/230V	Matt White
2 811 35MG	230V	120/230V	Matt Grey
2 811 35MB	230V	120/230V	Matt Black
2 811 35DS	230V	120/230V	Dark Silver
2 811 35CH	230V	120/230V	Champagne
2 811 35DB	230V	120/230V	Dark Bronze
2 811 35BA	230V	120/230V	Brushed Aluminium
2 811 35BB	230V	120/230V	Brushed Black
2 821 35	230V	120/230V	Matt black without plate
2 831 35	230V	120/230V	Silver without plate
2 833 35	230V	120/230V	Pearl without plate
2 835 35	230V	120/230V	Dark silver without plate
2 839 35	230V	120/230V	Champagne without plate

Cover plates (2 x 1 gang)

Reference	Color of enclosure
2 819 01	White
2 819 06	Silver
2 819 11	Champagne
2 819 51	Pearl
2 819 56	Dark silver
2 819 61	Brass
2 819 66	Bronze
2 819 71	Matt black
2 819 76	Copper
2 819 79	Metal BSS
2 819 83	Metal gold
2 819 87	Metal PSS
2 819 91	Metal Lacquered black



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 11/06/2025

Signature:



ANNEX

CLASSIFICATION

Frequency	50 / 60 Hz
Supply	230 V~
Output	120 / 230 V
Power output	20 VA
Class	I
Short-circuit protection	Non-inherently short-circuit proof
Degree of protection	IP24
Mobility	Stationary
Time of operation	Continuous
Intended use	Associated for specific use
Rated maximum ambient temperature	25°C
Windings	Class A
Output connection	Socket
Terminals (Supply)	Screwless



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE

33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr

Date: 11/06/2025

Signature

