



Ref. Certif. No.

FR_719203

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Fixed switched socket-outlet

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, Huizhou, 516001
Guangdong - CHINA

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

Note: When more than one factory, please report on page 2

☒ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

AC3143MW, AC3143MT, AC3143MB

Additional information (if necessary may also be reported on page 2)

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022

As shown in the Test Report Ref. No. which forms part of this Certificate

ARLI-ESH-P24020238

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 04/06/2024



LABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 15,745,984 €
RCS Nanterre B 408 363 174
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES

Signature:
Julien GAUTHIER
Certification Officer

ANNEX

Name and address of the factories:**Legrand Intelligent Electrical (Huizhou) Co., Ltd.**

Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, 516001
Guangdong - CHINA

LEGRAND FRANCE

128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY 87045 LIMOGES CEDEX - FRANCE

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD

A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. - NASHIK - 422113, MAHARASHTRA - INDIA



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE

33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr



Date: 04/06/2024

Signature: **Julien GAUTHIER**
Certification Officer

ANNEX

References, ratings and main characteristics:

All the commercial references listed below may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ... In this case, the products are technically the same.

CLASSIC references								
Type reference	White Commercial ref	Titanium Commercial ref	Black Commercial ref	Rated values	Pattern	Actuating g	Module	Specificities
T003718AA	AC3143MW	AC3143MT	AC3143MB	5A, 250VAC	..	Plug in of device.	2	

Characteristics of appliance

Protection of degree	IP20
Method of actuating	Plug in device with the socket
Method of mounting	flush type
Type of terminals	screw type
Existing of Shutters	with Shutters
Rated current (A)	5A
Rated voltage (V)	250V~

Frame


Commercial ref	Designation
A1402	1G 1 AND 2M BRITISH STD FRAME
A1403	1G 1 AND 2M BS FRAME W/ EARTH
A1404	1G 3M HORIZO/VERTICAL BS FRAME
A1408	2G 3M BS FRAME
A1409	2G 2 X 2M BS FRAME
A1406	3M IT/FR/SCH FRAME
A1407	6M IT/FR/SCH FRAME
A1401	2M PANEL MOUNTING SUPPORT
A1405	4M FR/SCH FRAME

Blank

Commercial ref			Designation
Matt White	Matt Titanium	Matt Black	
AC150MW	AC150MT	AC150MB	1 BLANK MODULE
AC153MW	AC153MT	AC153MB	2 BLANK MODULES
AC1501MW	AC1501MT	AC1501MB	1G BS BLANKING PLATE
AC1502MW	AC1502MT	AC1502MB	2G BS BLANKING PLATE



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr



Date: 04/06/2024

Signature: **Julien GAUTHIER**
Certification Officer

ANNEX

Cover plates

Commercial ref									
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium	Designation
AC1104MW	AC1104MT	AC1104MB	AC1104FW	AC1104FB	AC1104DA	AC1104BS	AC1104NB	AC1104SA	1G 3M BS HORIZ/ VERT PLATE
AC1105MW	AC1105MT	AC1105MB	AC1105FW	AC1105FB	AC1105DA	AC1105BS	AC1105NB	AC1105SA	3M BS PLATE FOR 2G BOX
AC1107MW	AC1107MT	AC1107MB	AC1107FW	AC1107FB	AC1107DA	AC1107BS	AC1107NB	AC1107SA	3M IT/US PLATE
AC1108MW	AC1108MT	AC1108MB	AC1108FW	AC1108FB	AC1108DA	AC1108BS	AC1108NB	AC1108SA	2 X 2M BS PLATE
AC1110MW	AC1110MT	AC1110MB	AC1110FW	AC1110FB	AC1110DA	AC1110BS	AC1110NB	AC1110SA	4M IT/FR/ SCH PLATE
AC1111MW	AC1111MT	AC1111MB	AC1111FW	AC1111FB	AC1111DA	AC1111BS	AC1111NB	AC1111SA	6M IT/FR/ SCH PLATE
AC1201MW	AC1201MT	AC1201MB	AC1201FW	AC1201FB	AC1201DA	AC1201BS	AC1201NB	AC1201SA	2M PLATE+FRAME
AC1202MW	AC1202MT	AC1202MB	AC1202FW	AC1202FB	AC1202DA	AC1202BS	AC1202NB	AC1202SA	3M PLATE+FRAME
AC1203MW	AC1203MT	AC1203MB	AC1203FW	AC1203FB	AC1203DA	AC1203BS	AC1203NB	AC1203SA	4M PLATE+FRAME
AC1204MW	AC1204MT	AC1204MB	AC1204FW	AC1204FB	AC1204DA	AC1204BS	AC1204NB	AC1204SA	6M BS PLATE+FRAME
AC1205MW	AC1205MT	AC1205MB	AC1205FW	AC1205FB	AC1205DA	AC1205BS	AC1205NB	AC1205SA	6M PLATE+FRAME
AC1206MW	AC1206MT	AC1206MB	AC1206FW	AC1206FB	AC1206DA	AC1206BS	AC1206NB	AC1206SA	8M PLATE+FRAME
AC1207MW	AC1207MT	AC1207MB	AC1207FW	AC1207FB	AC1207DA	AC1207BS	AC1207NB	AC1207SA	8M PLATE+FRAME
AC1208MW	AC1208MT	AC1208MB	AC1208FW	AC1208FB	AC1208DA	AC1208BS	AC1208NB	AC1208SA	2 X 4M PLATE+FRAME
AC1209MW	AC1209MT	AC1209MB	AC1209FW	AC1209FB	AC1209DA	AC1209BS	AC1209NB	AC1209SA	2 X 6M BS PLATE+FRAME
AC1210MW	AC1210MT	AC1210MB	AC1210FW	AC1210FB	AC1210DA	AC1210BS	AC1210NB	AC1210SA	2 X 6M PLATE+FRAME
AC1211MW	AC1211MT	AC1211MB	---	---	---	---	---	---	3 X 6M PLATE+FRAME
---	---	---	AB1100FW	AB1100FB	AB1100DA	AB1100BS	AB1100NB	AB1100SA	4M HYBRID PLATE 2M + 2M SWITCH
---	---	---	AB1200FW	AB1200FB	AB1200DA	AB1200BS	AB1200NB	AB1200SA	6M HYBRID PLATE 3M + 2M DIMMER
---	---	---	AB1201FW	AB1201FB	AB1201DA	AB1201BS	AB1201NB	AB1201SA	6M HYBRID PLATE 3M + 2M SWITCH
---	---	---	AB1202FW	AB1202FB	AB1202DA	AB1202BS	AB1202NB	AB1202SA	6M HYBRID PLATE+FRAM 3M+2M DIM
---	---	---	AB1203FW	AB1203FB	AB1203DA	AB1203BS	AB1203NB	AB1203SA	6M HYBRID PLATE+FRAM 3M +2M SW
---	---	---	AB1204FW	AB1204FB	AB1204DA	AB1204BS	AB1204NB	AB1204SA	6M HYBRID PLATE 4M + 1M SWITCH
---	---	---	AB1205FW	AB1205FB	AB1205DA	AB1205BS	AB1205NB	AB1205SA	6M HYBRID PLATE+FRAME 4M+1M SW
---	---	---	AB1206FW	AB1206FB	AB1206DA	AB1206BS	AB1206NB	AB1206SA	8M HYBRID PLATE 5M +2M DIMMER
---	---	---	AB1207FW	AB1207FB	AB1207DA	AB1207BS	AB1207NB	AB1207SA	8M HYBRID PLATE+FRAM 5M+2M DIM
AC1118MW	AC1118MT	AC1118MB	AC1118FW	AC1118FB	AC1118DA	AC1118BS	AC1118NB	AC1118SA	4X4 US PLATE FOR 2M
AC1212MW	AC1212MT	AC1212MB	---	---	---	---	---	---	9M PLATE+FRAME
AC1213MW	AC1213MT	AC1213MB	---	---	---	---	---	---	2 X 8M PLATE+FRAME
---	---	---	AB1208FW	AB1208FB	AB1208DA	AB1208BS	AB1208NB	AB1208SA	4M HYBRID PLATE+FRAME 2M + 2M SWITCH



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr



LABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 15.745.984 €
RCS Nanterre B 408 631 124
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES

Signature: *Julien GAUTHIER*
Certification Officer


Date: 04/06/2024

ANNEX

standard Sheet:	BS 546
rated current (A)	5A
rated load (W)	-
rated voltage (V)	250V~
household voltage (V)	-
degree of protection	IP20
provision for earthing	with earthing contact
method of connecting the cable	rewirable
type of terminals	screw-type
type of connections	-
socket-outlets	
multiple socket-outlets	5A: 1
number of socket-outlets	
degree of protection against electric shock	normal protection
existence of shutters	with shutters
method of application - mounting	flush-type
method of installation	design A
plugs:	
class of equipment	-
entry of cable	-



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr



Date: 04/06/2024

Signature: **Julien GAUTHIER**
Certification Officer