

## IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product

Socket-outlets for fixed installations

Name and address of the applicant

**LEGRAND FRANCE**  
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY,  
87045 LIMOGES CEDEX - FRANCE

Name and address of the manufacturer

**LEGRAND FRANCE**  
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY,  
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

**LEGRAND MAGYARORSZAG VILLAMOSSAGI RENDSZEREK ZRt**  
IPARTELEPI UT 14 PF 10, 6600 SZENTES - HUNGARY

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

0 695 85, 0 697 32, 0 697 39, 0 697 50

Additional information (if necessary may also be reported on page 2)

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2002(ed.3) +A1:2006 +A2:2013


As shown in the Test Report Ref. No. which forms part of this Certificate

ABND-ESH-P20090653

This CB Test Certificate is issued by the National Certification Body

LCIE – Laboratoire Central des Industries Electriques  
33, avenue du Général Leclerc – BP8  
FR 92 266 Fontenay aux Roses Cedex  
[www.lcie.fr](http://www.lcie.fr)

Date: 22/12/2020

Signature:  **Jérôme REYSSON**  
Certification Officer

## ANNEX

## RATING AND MAIN CHARACTERISTICS

Reference	Range*	Description 1	Description 2
0 695 85	PLEXO55 1G UNSW COMPOSABLE	PRISE 13A BS COMPO.GRISE	with 1 socket-outlet, without enclosure; Compatible with enclosure of 0 697 32, 0 697 39 & 0 697 50
0 697 32	PLEXO55 1G UNSW	PRISE 13A BS COMPLETE GRISE	with 1 socket-outlet,
0 697 39	PLEXO55 2G UNSW	PRISE 2X2P+T H 13A BS COMPL.	with 2 socket-outlets,
0 697 50	PLEXO55 2G UNSW	2P+T BS 13A+VV 10AX 2PH GRIS	with 1 socket-outlet & 1 switch (10AX)

\* The "Range" denotes applicant's categorization.

## CLASSIFICATION

standard Sheet:	standard sheet of BS 1363-2	
rated current (A)	13A	
rated voltage (V)	250V	
degree of protection	IP55	
provision for earthing	with earthing contact	
method of connecting the cable	rewirable	
type of terminals	screw-type	
colour	Grey	
<b>socket-outlets</b>		
multiple socket-outlets	13A : 1 or 2	
number of socket-outlets		
degree of protection against electric shock	increased protection	
existence of shutters	with shutters	
method of application - mounting	Surface-type	
method of installation	design B	
type of components	manufacturer	Certification
10AX switch	Legrand	LCIE CB FR_707086/M1



LCIE – Laboratoire Central des Industries Electriques  
33, avenue du Général Leclerc – BP8  
FR 92 266 Fontenay aux Roses Cedex  
[www.lcie.fr](http://www.lcie.fr)

Date: 22/12/2020

Signature

