



Ref. Certif. No.

ES1842-M1-AENOR

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

LED LUMINAIRES FOR EMERGENCY LIGHTING

Name and address of the applicant

LEGRAND GROUP ESPAÑA, S.L.
CL HIERRO, 56
28850 TORREJON DE ARDOZ (Madrid - Spain)

Name and address of the manufacturer

SAME AS ABOVE

Name and address of the factory

SAME AS ABOVE

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark (if any)

LEGRAND

Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

See references on the Annex

Additional information (if necessary may also be reported on page 2)

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60598-1:2014
IEC 60598-1:2014/A1:2017
IEC 60598-2-22:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

2016120782B1, 2020040168B1-M1

This CB Test Certificate is issued by the National Certification Body

AENOR INTERNACIONAL S.A.U.
Cl Génova, 6
ES-28004 MADRID (SPAIN)

Date: 2020-11-16

Signature: 
Rafael GARCÍA MEIRO
Chief Executive Officer

ANNEX TO CB CERTIFICATE N° ES1842-M1-AENOR

CERTIFIED REFERENCES AND THEIR PRINCIPAL CHARACTERISTICS

Product: LED LUMINAIRES FOR EMERGENCY LIGHTING

Trade Mark: LEGRAND

Type reference	Rated voltage and frequency	N° lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
660620	230 V~; 50/60 Hz	LED 2 x 0,25 W	70 lm - 1 h	2,4 V 0,8 Ah NiCd 2 elementos / cells	Non maintained; remote rest	Electronic protection. URA-ONE Autotest
660621	230 V~; 50/60 Hz	LED 2 x 0,25 W	100 lm - 1 h	2,4 V 0,8 Ah NiCd 2 elementos / cells	Non maintained; remote rest	Electronic protection. URA-ONE Autotest
660623	230 V~; 50/60 Hz	LED 4 x 0,25 W	200 lm - 1 h	2,4 V 1,5 Ah NiCd 2 elementos / cells	Non maintained; remote rest	Electronic protection. URA-ONE Autotest
660624	230 V~; 50/60 Hz	LED 4 x 2 W	350 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	Non maintained; remote rest	Electronic protection. URA-ONE Autotest
660625	230 V~; 50/60 Hz	LED 4 x 1 W	500 lm - 1 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Non maintained; remote rest	Electronic protection. URA-ONE Autotest
661625	230 V~; 50/60 Hz	LED 4 x 2 W	500 lm - 1 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Non maintained; remote rest	Electronic protection. URA-ONE
661637	120 V~; 50/60 Hz	LED 4 x 0,25 W	160 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	Non maintained; remote rest	Electronic protection. URA-ONE 120VAC
661638	120 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	Non maintained; remote rest	Electronic protection. URA-ONE 120VAC
661640	230 V~; 50/60 Hz	LED 4 x 0,5 W	100 lm - 3 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Maintained, possible non maintained; remote rest	Electronic protection. URA-ONE
662640	230 V~; 50/60 Hz	LED 4 x 0,5 W	100 lm - 3 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Maintained, possible non maintained; remote rest	Electronic protection. URA-ONE LVS

IP degree of protection: IP 42; IK 07

Power supply connection means: Terminals

Classif. per holding surface material: Suitable for normally flammable surfaces

Protection against electric shocks (class): Class II