



## ZODZ.E212478 Positioning Devices

[Page Bottom](#)

### Positioning Devices

[See General Information for Positioning Devices](#)**LEGRAND FRANCE**

RUE PAUL-NOUEL

76770 MALAUNAY, FRANCE

E212478

#### Metallic Cable Ties Investigated to ANSI/UL 62275

Cat. No.	Type Dsg	Bundle Diam, mm (in.)		Loop Tensile Strength, N (lbf)	Operating Temp, °C (°F)		Min Installation Temp, °C (°F)	Resistant to UV Light	Plenum Rating	ANSI/UL 94 Mtl Flame Rating
		Min	Max		Min	Max				
31820, 387101	21	3	20	80	-40	85 or 105	0	No	No	V-2
31800, 387201	21	3	20	80	-40	85	0	Yes	No	V-2
387102	21	3	32	80	-40	85 or 105	0	No	No	V-2
387202	21	3	32	80	-40	85	0	Yes	No	V-2
31821, 387103	21	4	39	80	-40	85 or 105	0	No	No	V-2
31801, 387203	21	4	39	80	-40	85	0	Yes	No	V-2
31822, 387104	21	4	50	80	-40	85 or 105	0	No	No	V-2
31802, 387204	21	4	50	80	-40	85	0	Yes	No	V-2
31823, 387105	21	3	31	180	-40	85 or 105	0	No	No	V-2
31803, 387205	21	3	31	180	-40	85	0	Yes	No	V-2
31824, 387106	21	5	47	180	-40	85 or 105	0	No	No	V-2
31804, 387206	21	5	47	180	-40	85	0	Yes	No	V-2
31825, 387107	21	7	75	180	-40	85 or 105	0	No	No	V-2
31805, 387207	21	7	75	180	-40	85	0	Yes	No	V-2
31826	21	7	96	180	-40	85 or 105	0	No	No	V-2
31806	21	7	96	180	-40	85	0	Yes	No	V-2
31827, 387110	21	4	45	220	-40	85 or 105	0	No	No	V-2
31807, 387210	21	4	45	220	-40	85	0	Yes	No	V-2
387111	21	5	47	220	-40	85 or 105	0	No	No	V-2
31828, 387112	21	7	76	220	-40	85 or 105	0	No	No	V-2

31808, 387212	21	7	76	220	-40	85	0	Yes	No	V-2
31829, 387113	21	7	96	220	-40	85 or 105	0	No	No	V-2
31809, 387213	21	7	96	220	-40	85	0	Yes	No	V-2
387114	21	7	101	220	-40	85 or 105	0	No	No	V-2
387214	21	7	101	220	-40	85	0	Yes	No	V-2
31833	21	7	115	220	-40	85 or 105	0	No	No	V-2
31813	21	7	115	220	-40	85	0	Yes	No	V-2
31830, 387115	21	7	47	530	-40	85 or 105	0	No	No	V-2
31810, 387215	21	7	47	530	-40	85	0	Yes	No	V-2
31834, 387116	21	8	73	530	-40	85 or 105	0	No	No	V-2
31814, 387216	21	8	73	530	-40	85	0	Yes	No	V-2
31831, 387117	21	8	96	530	-40	85 or 105	0	No	No	V-2
31811, 387217	21	8	96	530	-40	85	0	Yes	No	V-2
31835, 32045, 387118	21	15	147	530	-40	85 or 105	0	No	No	V-2
31815, 32025, 387218	21	15	147	530	-40	85	0	Yes	No	V-2
31836, 32046, 387119	21	12	208	800	-40	85 or 105	0	No	No	V-2
31816, 32026, 387219	21	12	208	800	-40	85	0	Yes	No	V-2
31837, 32048	21	12	223	800	-40	85 or 105	0	No	No	V-2
31817, 32027	21	12	223	800	-40	85	0	Yes	No	V-2
31838, 32051	21	15	285	1 150	-40	85 or 105	0	No	No	V-2
31818, 32028	21	15	285	1 150	-40	85	0	Yes	No	V-2
387211	21	5	47	220	-40	85	0	Yes	No	V-2

Last Updated on 2015-02-24

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2015 UL LLC

When the UL Leaf Mark is on the product, or when the word "Environment" is included in the UL Mark, please search the [UL Environment database](#) for additional information regarding this product's certification.

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2015 UL LLC".