



Ref. Certif. No.

FR_719959/M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Combined socket-outlet and switch
Switched socket-outlets for fixed installations

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, Huizhou 516001, Guangdong -
CHINA

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

Note: When more than one factory, please report on page 2

☒ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_719959 dated 03/09/2024.
Update the list of product references
Update the list of components

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022
IEC 60884-2-3:2006

As shown in the Test Report Ref. No. which forms part of this Certificate

ARLI-ESH-P25030142

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 17/04/2025

Signature: 
Julien CAUTHIER
Certification Officer



ANNEX

Name and address of the factories:

Legrand Intelligent Electrical (Huizhou) Co., Ltd.

Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou 516001, Guangdong - CHINA

LEGRAND

AVENUE DU PARC ALATA - 60550 VERNEUIL EN HALATTE – FRANCE

RAIS HASSAN SAADI Logistics Dubai

Jebel Ali Free Zone, P.O. Box 7 Dubai - UNITED ARAB EMIRATES

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD

A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. NASHIK - 422113, MAHARASHTRA – INDIA

References, ratings and main characteristics:

Reference	Range*	Product description	Color of enclosure	USB module
AA3320MW	Altair	2G BS 13A SP SWITCHED + USB A+C 27W	Matt White	B005398DA B006854AA
AA3320MB			Matt Black	
AA3320MT			Matt Titanium	
AA3320CH			Champagne	
AA3320DB			Dark Bronze	
AA3320RS			Rose	
AA3321MW		2G BS 13A DP SWITCHED + USB A+C 27W	Matt White	
AA3321MB			Matt Black	
AA3321MT			Matt Titanium	
AA3321CH			Champagne	
AA3321DB			Dark Bronze	
AA3321RS			Rose	
AA3327MW		2G BS 13A SP SWITCHED + USB A+C 27W with microswitch	Matt White	B005398FA B006854BA
AA3327MB			Matt Black	
AA3327MT			Matt Titanium	
GA33033CH	New galion	2G BS 13A SP SWITCHED SOCKET + USB A+C 27W	CHAMPAGNE	B005398DA B006854AA
GA33033DS			DARK SILVER	
GA33033MB			MATT BLACK	
GA33033GR			GRAPHITE	
GA33033MW			MATT WHITE	
GA33035CH		2G BS 13A SP SWITCHED + USB A+C 27W with microswitch	CHAMPAGNE	B005398FA B006854BA
GA33035DS			DARK SILVER	
GA33035MB			MATT BLACK	
GA33035GR			GRAPHITE	
GA33035MW			MATT WHITE	

*The "range" denotes applicant's categorization



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE

33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr



Date: 17/04/2025

Signature: **Julien GAUTHIER**
Certification Officer

ANNEX

Additional information for AA332*** series:

All the commercial references listed below may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ... In this case, the products are technically the same.

Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Rated values	Switch	Actuating	Gang	Specificities
AA3320 MW	AA3320 MB	AA3320 MT	AA3320 CH	AA3320 DB	AA3320RS	13A 250V~ USB: 5Vdc- 20Vdc, Max. 27W	Single pole	Rock er	2	USB port: A+C
AA3327 MW	AA3327 MB	AA3327 MT	-	-	-		Single pole	Rock er	2	USB port: A+C PCBA with micro switch
AA3321 MW	AA3321 MB	AA3321 MT	AA3321 CH	AA3321 DB	AA3321RS		Double pole	Rock er	2	USB port: A+C

Cover plates

Commercial ref										Designation
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium		
AA1115 MW	AA1115MT	AA1115 MB	AA1115FW	AA1115FB	AA1115DA	AA1115BS	AA1115NB	AA1115SA		2G BS PLATE 2X13A SW SKT +2USB
Champagne	Dark Bronze	Rose	Brushed Bronze	Brushed Antique Brass	Solid Dark Bronze	Solid Sand	Solid Black	Solid Rose	Solid Champagne	
AA1115 CH	AA1115DB	AA1115RS	AA1115BB	AA1115AB	AA1115SZ	AA1115SD	AA1115SB	AA1115SR	AA1115SC	2G BS PLATE 2X13A SW SKT +2USB



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 17/04/2025

Signature: 
Certification Officer



ANNEX

CLASSIFICATION

standard Sheet:	BS 1363-2
rated current (A)	13A
rated load (W)	-
rated voltage (V)	250V~
household voltage (V)	-
degree of protection	IP20
provision for earthing	with earthing contact
method of connecting the cable	rewirable
type of terminals	screw-type
type of connections	-
socket-outlets	
multiple socket-outlets	13A: 2
number of socket-outlets	
degree of protection against electric shock	normal protection
existence of shutters	with shutters
method of application - mounting	flush-type
method of installation	design A
plugs:	
class of equipment	-
entry of cable	-

type of components	manufacturer	Certification
USB charger	LEGRAND FRANCE	KST test report No.: KST240418S006Q01
Alternative	LEGRAND FRANCE	LCIE TEST REPORT No.: ARLI-ESH- P25030145



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 17/04/2025

Signature:


LABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 15.745.984 €
RCS Nanterre B 409 263 174
F - 92266 FONTENAY-AUX-ROSES
Certification Officer