

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**CB TEST CERTIFICATE**

Product	Three and Four poles Switch Disconnecter
Name and address of the applicant	LEGRAND SNC 128 avenue du Maréchal de Lattre de Tassigny 87045 Limoges Cedex (France)
Name and address of the manufacturer	Same as applicant
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	See page 2
Ratings and principal characteristics	Ue=220-690V (50.0-60.0Hz) – Ie=125A Icw=1.50kA (1.00s) – Icm=2.50kA, Pattern No. 3 and 4
Trademark (if any)	Legrand
Customer's Testing Facility (CTF) Stage used	CTF Stage 2
Model / Type Ref.	DPX ³ -I 125 HP
Additional information (if necessary may also be reported on page 2)	See page 2
A sample of the product was tested and found to be in conformity with	IEC 60947-3:2020
As shown in the Test Report Ref. No. which forms part of this Certificate	2026733STO-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamnsgatan 43
Box 1103
SE-164 22 Kista, Sweden



Signature:



Henrik Wikström

Date: 09 March, 2021

Factories

Bticino S.p.a. – Via dei Folzoni, 5 – 24052, Azzano, San Paolo, Bergamo (Italy)

Legrand Low Voltage Electrical (Wuxi) CO., LTD, No.88, Ximei Road, New Zone, Wuxi, Jiangsu Province (P.R. China)

Novateur Electrical & Digital Systems Private Limited, D-4, MIDC Area, Jalgaon-425003 Maharashtra

Additional information

Characteristics:

Voltage ratings $U_e=220-690V$ (50-60Hz)

Rated current $I_e=125A$

$U_{imp} = 8kV$ $U_i = 800V$

Utilization Category: AC23A

U_e (V)	I_e (A)	I_{cm} (kA)	I_{cw} (1s) (kA)
415	125	2,5	1,5
690	125	2,5	1,5

Date: 09 March, 2021

Signature:

