

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Name and address of the applicant

Name and address of the manufacturer

Name and address of the factory

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

Trademark / Brand (if any)

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

Additional information (if necessary may also be reported on page 2)

A sample of the product was tested and found to be in conformity with

As shown in the Test Report Ref. No. which forms part of this Certificate

Intermediate adaptor

LEGRAND FRANCE128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE**LEGRAND FRANCE**128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE**BTICINO SPA**4 VIA LUCIANO MANARE
22036 ERBA
ITALY☐ Additional Information on page 2

See Annex



/

Type ZLS31 Reference : 0 648 87

Supersedes CBTC FR_707063 dated 22/10/2019.
Change of factory☐ Additional Information on page 2IEC 60884-1:2002 +A1:2006 +A2:2013
IEC 60884-2-5:2017

171369-762172B

This CB Test Certificate is issued by the National Certification Body

LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr

Date: 11/08/2021

Signature: 
Certification Officer

ANNEX

Mechanisms

Type reference	References	Nominal characteristics	Pattern	contact opening
ZLS31	0 648 87	16A 240V~	2 P+E	micro

Characteristics of appliances

Standard Sheet:	V CEE7 (Socket-outlet) and VII CEE7 (Plug)
Degree of protection	IP20
Protection for earthing	with earth contact
Degree of protection against the electric shocks	Normal protection
Presence of shutters	with shutters
Method of mounting	Portable-type
Pattern number	1
Method of actuating	Push button or other internal influences

Rated current (A) - rated load (VA or W) : for 240 V~

300 W halogen lamps
60 W LED or 10 lamps
60 W fluorescent compact lamps
300 VA feromagnetic transformers for ELV halogen lamps
300 VA electronic transformers for ELV halogen lamps

Minimum current (A) - minimum load (VA or W) :	5 W
Rated voltage (V)	240 V
Rated frequency (Hz)	50/60 Hz



LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr



Signature: **Gilles LEMONNIER**
Certification Officer

Date: 11/08/2021