

# AENOR

Confía

ENEC Certification Body registered under ID # 01. For further information, please consult [www.enec.com](http://www.enec.com)

# LICENCE

to use the European Mark



**Licence Nr.** ENEC/000993

**Under the conditions given in the following pages of this document, the licence to use the ENEC Mark in conjunction with the suffix 01, as shown above, has been issued to:**

LEGRAND GROUP ESPAÑA, S.L.  
CL HIERRO, 56  
28850 TORREJON DE ARDOZ (Madrid – España / Spain)

**For the product(s):**

LED luminaires for emergency lighting

**Trade name(s):**

LEGRAND

**Complying with the following European Standards:**

EN 60598-2-22:2014; EN 60598-2-22:2014/A1:2020  
EN IEC 60598-1:2021  
EN 62262:2002

A handwritten signature in blue ink, appearing to read 'Rafael Garcia', written over a horizontal line.

**Date:** 2022-11-03

**Signature:**

**Name:** Rafael García  
**Position:** Chief Executive Officer

This licence has been issued under the presumption and conditional on the fact that the licensee holds all necessary legal rights with regard to the product presented for testing and certification.

AENOR INTERNACIONAL, S.A.U.  
Cl Génova, 6  
28004 MADRID (Spain)

## CERTIFICATE OF THE ENEC EUROPEAN MARK

Type of Product	LED LUMINAIRES FOR EMERGENCY LIGHTING
r1) Certificate n°	ENEC/000993
r2) Date of the Certificate	2022-11-03
r3) report n°	2016120784B1, 2019040178B1, 2020040169B1-M1, 2022070428B1
r4) Name and address of the licensee	LEGRAND GROUP ESPAÑA, S.L. CL HIERRO, 56 28850 TORREJON DE ARDOZ (Madrid - España / Spain)
r5) Address of the factory	CL HIERRO, 56 28850 TORREJON DE ARDOZ (Madrid - España / Spain)
r6) European Standard	EN 60598-2-22:2014; EN 60598-2-22:2014/A1:2020 EN IEC 60598-1:2021 EN 62262:2002
r7) Type reference	See above for details
r8) Trade Mark	LEGRAND
r9) Rated voltage and frequency	See above for details
r10) N° lamps x rated power, type and lampholder	See above for details
r11) IP degree of protection	IP 65; IK 07
r12) Power supply connection means	Bornes / terminals
r13) Classif. per holding surface material	Apta para superficies normalmente inflamables / suitable for normally flammable surfaces
r14) Protection against electric shocks (class)	Clase / class II
r15) Rated lumen output and duration	See above for details
r16) Battery features	See above for details
r17) Additional information	See above for details
r18) General data	See above for details
Date of expiry: 2025-04-30	This certificate supersedes certificate 007/000993, dated 2020-10-22.

## CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Rated voltage and frequency	N° lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
660426	230 V~; 50/60 Hz	LED 2 x 0,5 W	100 lm - 1 h	2,4 V 0,8 Ah NiCd 2 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B- 65 Autotest
660427	230 V~; 50/60 Hz	LED 4 x 0,5 W	200 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B- 65 Autotest
660428	230 V~; 50/60 Hz	LED 4 x 2 W	350 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B- 65 Autotest
660429	230 V~; 50/60 Hz	LED 4 x 1 W	500 lm - 1 h	4,8 V 2 Ah NiMH 4 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B- 65 Autotest
661425	230 V~; 50/60 Hz	LED 2 x 0,5 W	70 lm - 1 h	2,4 V 0,8 Ah NiCd 2 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B- 65
661426	230 V~; 50/60 Hz	LED 2 x 0,5 W	100 lm - 1 h	2,4 V 0,8 Ah NiCd 2 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B- 65

## CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Rated voltage and frequency	N° lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
661427	230 V~; 50/60 Hz	LED 4 x 0,5 W	200 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B-65
661428	230 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B-65
661429	230 V~; 50/60 Hz	LED 4 x 2 W	500 lm - 1 h	4,8 V 2 Ah NiMH 4 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B-65
661431	230 V~; 50/60 Hz	LED 4 x 0,5 W	100 lm - 1 h	2,4 V 1,5 Ah NiCd 2 elementos / cells	Permanente / maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B-65
661433	230 V~; 50/60 Hz	LED 4 x 1 W	200 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	Permanente / maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B-65
661434	230 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	Permanente / maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B-65
661437	120 V~; 50/60 Hz	LED 4 x 0,5 W	160 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	Permanente / maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B-65 120VAC

## CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Rated voltage and frequency	N° lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
661438	120 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	Permanente / maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B-65 120VAC
661440	230 V~; 50/60 Hz	LED 4 x 0,5 W	100 lm - 3 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Permanente / maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B-65
662431	230 V~; 50/60 Hz	LED 4 x 0,5 W	100 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	Permanente / maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B-65 LVS
662433	230 V~; 50/60 Hz	LED 4 x 1 W	200 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	Permanente / maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B-65 LVS
662434	230 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 1 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Permanente / maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B-65 LVS
662440	230 V~; 50/60 Hz	LED 4 x 0,5 W	100 lm - 3 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Permanente / maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. B-65 LVS