

LICENCE

to use the European Mark



Licence Nr. ENEC/001088

Under the conditions given in the following pages of this document, the licence to use the ENEC Mark in conjunction with the suffix 01, as shown above, has been issued to:

LEGRAND GROUP ESPAÑA, S.L.
CL HIERRO, 56
28850 TORREJON DE ARDOZ (Madrid – España / Spain)

For the product(s):

LED luminaires for emergency lighting

Trade name(s):

LEGRAND

Complying with the following European Standards:

EN IEC 60598-1:2021; EN 60598-2-22:2014;
EN 60598-2-22:2014/A1:2020; EN 62262:2002

Date: 2022-11-11

Signature:

A handwritten signature in blue ink, appearing to read 'Rafael García', with a long horizontal stroke extending to the right.

Name: Rafael García
Position: Chief Executive Officer

This licence has been issued under the presumption and conditional on the fact that the licensee holds all necessary legal rights with regard to the product presented for testing and certification.

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type of Product	LED LUMINAIRES FOR EMERGENCY LIGHTING
r1) Certificate n°	ENEC/001088
r2) Date of the Certificate	2022-11-11
r3) report n°	2017090608B1, 2022070431B1
r4) Name and address of the licensee	LEGRAND GROUP ESPAÑA, S.L. CL HIERRO, 56 28850 TORREJON DE ARDOZ (Madrid - España / Spain)
r5) Address of the factory	PI AVANZADO, AV DE LA CIENCIA, S/N 13005 CIUDAD REAL (España / Spain)
r6) European Standard	EN IEC 60598-1:2021; EN 60598-2-22:2014; EN 60598-2-22:2014/A1:2020; EN 62262:2002
r7) Type reference	See above for details
r8) Trade Mark	LEGRAND
r9) Rated voltage and frequency	230 V~; 50 Hz
r10) N° lamps x rated power, type and lampholder	1 x 3 W; LED; módulo / panel
r11) IP degree of protection	IP 20; IK 04
r12) Power supply connection means	Bornes / terminals
r13) Classif. per holding surface material	Apta para superficies normalmente inflamables / suitable for normally flammable surfaces
r14) Protection against electric shocks (class)	Clase / class II
r15) Rated lumen output and duration	See above for details
r16) Battery features	See above for details
r17) Additional information	Protección por fusible / fuse protection
r18) General data	No permanente / non maintained; puesta en reposo remota / remote rest; familia / series URA SPOT
Date of expiry: 2025-04-30	This certificate supersedes certificate 007/001088, dated 2018-05-23.

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Rated lumen output and duration	Battery features
661860	170 lm; 1 h	Ni-Cd 3,6 V 0,8 Ah 3 elementos / cells
661861	170 lm; 1 h	Ni-Cd 3,6 V 0,8 Ah 3 elementos / cells
661864	100 lm; 3 h	Ni-Cd 3,6 V 1,6 Ah 3 elementos / cells
661865	100 lm; 3 h	Ni-Cd 3,6 V 1,6 Ah 3 elementos / cells