

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Switched socket-outlet (flush-type)
Name and address of the applicant	Legrand Intelligent Electrical (Huizhou) Co., Ltd. Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, P.R. China
Name and address of the manufacturer	LEGRAND FRANCE 128, Avenue du Maréchal de Lattre de Tassigny, 87045 Limoges Cedex, France
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	Same as applicant
Ratings and principal characteristics	13A 250V~, IP20
Trademark (if any)	See page 2
Customer's Testing Facility (CTF) Stage used	-
Model / Type Ref.	See page 2
Additional information (if necessary may also be reported on page 2)	See page 2
A sample of the product was tested and found to be in conformity with	IEC 60884-1:2002+A1+A2 IEC 60884-2-3:2006
As shown in the Test Report Ref. No. which forms part of this Certificate	220101706SHA-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamnsgatan 43
Box 1103
SE-164 22 Kista, Sweden

intertek
Signature: 

Hyden Li

Date: 19 May, 2022



Ref. Certif. No.

SE-108083

Trademark (if any)



or tenby for 8 380 82



for other models

Model / Type Ref.

281117MW, 281117MG, 281117MB, 281117DS, 281117CH, 281117DB, 281117BA, 281117BB, 281119MW, 281119MG, 281119MB, 281119DS, 281119CH, 281119DB, 281119BA, 281119BB, 6 176 48, 6 177 48, 6 178 48, 6 180 48, 282487, 282487-C, 282487-C1, 282487-C2, 282487-C3, 8 380 82.

Additional information

13A 250V~, flush type, IP20, Class I, rewirable, with screw-type terminals, with 2 gang switched socket outlets comply with type G (configuration of BS 1363-2), with shutters, with one double pole switch for each socket-outlet, with plastic cover plate or plastic lining combined with metal sheet cover plate, with or without metal frame, with or without indicator lamp.

Total 26 models:

- 6 176 48: with white front cover and plastic white cover plate, without metal frame;
- 6 177 48: with dark front cover and plastic dark cover plate, without metal frame;
- 6 178 48: with ivory front cover and plastic ivory cover plate, without metal frame;
- 281117MW: with dark front cover and matt white plastic cover plate, with metal frame;
- 281117MG: with dark front cover and matt grey plastic cover plate, with metal frame;
- 281117MB: with dark front cover and matt black plastic cover plate, with metal frame;
- 281117DS: with dark front cover and dark silver plastic cover plate, with metal frame;
- 281117CH: with dark front cover and champagne plastic cover plate, with metal frame;
- 281117DB: with dark front cover and dark bronze plastic cover plate, with metal frame;
- 281117BA: with dark front cover and plastic lining combined with brushed aluminium metal sheet cover plate, with metal frame;
- 281117BB: with dark front cover and plastic lining combined with brushed black metal sheet cover plate, with metal frame;
- 281119MW: with dark front cover and matt white plastic cover plate, with metal frame, with indicator lamp;
- 281119MG: with dark front cover and matt grey plastic cover plate, with metal frame, with indicator lamp;
- 281119MB: with dark front cover and matt black plastic cover plate, with metal frame, with indicator lamp;
- 281119DS: with dark front cover and dark silver plastic cover plate, with metal frame, with indicator lamp;
- 281119CH: with dark front cover and champagne plastic cover plate, with metal frame, with indicator lamp;
- 281119DB: with dark front cover and dark bronze plastic cover plate, with metal frame, with indicator lamp;
- 281119BA: with dark front cover and plastic lining combined with brushed aluminium metal sheet cover plate, with metal frame, with indicator lamp;
- 281119BB: with dark front cover and plastic lining combined with brushed black metal sheet cover plate, with metal frame, with indicator lamp.

- 6 180 48 and 8 380 82: similar to 6 176 48 except the shape of cover plate.
- 282487: similar to 281117MW except the shape of cover plate and without metal frame.
- 282487-C: similar to 282487 except the cover plate with matt black color.
- 282487-C1: similar to 282487 except the cover plate with rose gold color.
- 282487-C2: similar to 282487 except the cover plate with champagne color.
- 282487-C3: similar to 282487 except the cover plate with dark silver color.

Date: 19 May, 2022

Signature: 