



Ref. Certif. No.

FR_722636

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Socket-outlet for fixed-electrical installations
Socket-outlets for fixed installations

Name and address of the applicant

LEGRAND MAGYARORSZAG VILLAMOSSAGI RENDSZEREK ZRT.
IPARTELEPI UT 14, 6600 SZENTES - HUNGARY

Name and address of the manufacturer

LEGRAND MAGYARORSZAG VILLAMOSSAGI RENDSZEREK ZRT.
IPARTELEPI UT 14, 6600 SZENTES - HUNGARY

Name and address of the factory

Note: When more than one factory, please report on page 2

☒ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)

legrand

Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

ARTEOR range
See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_706408/M1 dated 20/09/2022.
Update further to the evolution of the standard(s)
Addition of factory(ies)

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022

As shown in the Test Report Ref. No. which forms part of this Certificate

ARFH-ESH-P25030945

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 25/11/2025

Signature



ANNEX

Name and address of the factories:

LEGRAND MAGYARORSZAG VILLAMOSSAGI RENDSZEREK ZRT.
IPARTELEPI UT 14 6600 SZENTES - HUNGARY

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD
A-2, SINNAR MALEGAON MIDC, NASHIK PUNE ROAD
NASHIK, MAHARASHTRA STATE 422113 - INDIA

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone
516001 Huizhou, Guangdong - CHINA



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 25/11/2025

Signature:



ANNEX

References, ratings and main characteristics:

Reference	Range*	Description	Color of enclosure	with cover plate	with support frame
5 721 11	ARTEOR	2P+E 13A British Standard unswitched 1 gang	White	5 752 10	5 760 03
5 726 11	ARTEOR	2P+E 13A British Standard unswitched 1 gang	Magnesium	5 713 12	5 760 03
5 700 38	ARTEOR	2P+E 13A British Standard unswitched 1 gang	Champagne	5 713 22	5 760 03
5 710 38	ARTEOR	2P+E 13A British Standard unswitched 1 gang	Alu	5 713 02	5 760 03
5 726 41	ARTEOR	2P+E 13A British Standard unswitched 1 gang	Red	5 752 10	5 760 03

* The "range" denotes applicant's categorization.

CLASSIFICATION

standard Sheet:	standard sheet of BS 1363-2
rated current (A)	13A
rated load (W)	-
rated voltage (V)	250V
household voltage (V)	-
degree of protection	IP20
provision for earthing	with earthing contact
method of connecting the cable	rewirable
type of terminals	screw-type
type of connections	-
colour	See the table above
socket-outlets	
multiple socket-outlets	
number of socket-outlets	13A : 1
degree of protection against electric shock	normal protection
existence of shutters	with shutters
method of application - mounting	flush-type
method of installation	design A



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 25/11/2025

Signature

