

IEC**IECEE**

®

TM

Ref. Certif. No.

FR_722435/M1**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME****CB TEST CERTIFICATE**

Product

Socket-outlet for fixed-electrical installations

Name and address of the applicant

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the factory

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

Series : PLEXO
References : See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_722435 dated 28/08/2025. Update the list of product references : New contacts for MIFA / MIFA2H / MIFA2V / MIFA3H type reference and removal of 4 references "with claws"

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022

As shown in the Test Report Ref. No. which forms part of this Certificate

29460112-818747

This CB Test Certificate is issued by the National Certification Body

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 17/02/2026

Signature:
Paola Forigra
Certification Officer

IEC**IECEE**

®

™

Ref. Certif. No.

FR_722435/M1**ANNEX****Name and address of the factories:****LEGRAND FRANCE**

128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

NOVEA

7 impasse Montgolfier
87200 SAINT JUNIEN
FRANCE

ADAPEI Charente ESAT de St CLAUD

54 rue du FARNAUD
16450 SAINT-CLAUD
FRANCE

LEGRAND MAGYARORSZAG VILLAMOSSAGI RENDSZEREK ZRT

IPARTELEPI UT 14 PF 10
6600 SZENTES
HUNGARY



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 17/02/2026

Signature: *Paola Forigra*
Certification Officer



ANNEX

References, ratings and main characteristics:

MECHANISMS

Type Ref.	Ref. Grey	Ref. White	Ref. Anthracite	Ref. Sand	Function	Characteristics	Type of terminals	Mounting	PRO / DIY	Specificities
MIFA	0 695 51L	0 696 21L	0 698 91L	0 698 28L	2P+T	16A 250V~	Screwless	/	PRO	Mechanism only
	0 700 42		0 700 47		2P+T	16A 250V~	Screwless	/	DIY	Mechanism only
	0 697 31L	0 697 81L	0 697 91L	0 697 76L	2P+T	16A 250V~	Screwless	surface type	PRO	Mechanism with box - Complete product
	0 700 03 0 700 04	0 700 24	0 700 27	0 700 69	2P+T	16A 250V~	Screwless	surface type	DIY	Mechanism with box - Complete product
	0 698 31L	0 698 70L	0 698 60L		2P+T	16A 250V~	Screwless	flush-type	PRO	Mechanism with frame - Complete product
	0 700 31L	0 700 34L	0 700 38L	0 700 75L	2P+T	16A 250V~	Screwless	flush-type	DIY	mechanism with frame - Complete product
MIFV	0 695 52L	0 696 24L	0 698 40L		2P+T	16A 250V~	Screw-type	/	PRO	Mechanism only
/	0 695 53L	0 696 23L			2P+T	16A 250V~	Screw-type	/	PRO	Tamperproof mechanism only
MIFA2H	0 695 62L	0 696 42L	0 698 42L		2 x 2P+T	16A 250V~	Screwless	/	PRO	Pre-wired mechanism only
	0 697 68L	0 697 78L	0 697 88L		2 x 2P+T	16A 250V~	Screwless	surface type	PRO	Pre-wired mechanism with box - Complete product
	0 700 05	0 700 25	0 700 64		2 x 2P+T	16A 250V~	Screwless	surface type	DIY	Pre-wired mechanism with box - Complete product
			0 697 49L		2 x 2P+T	16A 250V~	Screwless	surface type	PRO	Yard Stake - Complete product



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 17/02/2026

Signature:



ANNEX

Type Ref.	Ref. Grey	Ref. White	Ref. Anthracite	Ref. Sand	Function	Characteristics	Type of terminals	Mounting	PRO / DIY	Specificities
MIFA2V	0 695 63L	0 696 43L	0 698 43L		2 x 2P+T	16A 250V~	Screwless	/	PRO	Pre-wired mechanism only
	0 700 13	0 700 18	0 700 65		2 x 2P+T	16A 250V~	Screwless	surface type	DIY	Pre-wired mechanism with box - Complete product
MIFA3H	0 695 64L	0 696 44L	0 698 44L		3 x 2P+T	16A 250V~	Screwless	/	PRO	Pre-wired mechanism only
	0 697 63L		0 697 66L		3 x 2P+T	16A 250V~	Screwless	surface type	PRO	Pre-wired mechanism with box - Complete product
	0 700 14		0 700 66		3 x 2P+T	16A 250V~	Screwless	surface type	DIY	Pre-wired mechanism with box - Complete product

“All the commercial references listed above may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ...In this case, the products are technically the same.”



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 17/02/2026

Signature: *Paula Ferreira*



ANNEX

ACCESSORIES

References Grey	References White	References Anthracite	References Sand	References Other	Designation
0 696 51L	0 696 89L	0 696 01L	0 698 63L		Box 1 gang with membrane cable gland
0 700 50		0 700 56			Box 1 gang with membrane cable gland
0 696 72L	0 696 90L	0 696 02L	0 698 67L		Box 2 gang with membrane cable gland
0 700 51		0 700 57			Box 2 gang with membrane cable gland
0 696 80L	0 696 88L	0 696 03L			Box 3 gang with membrane cable gland
0 700 52		0 700 58			Box 3 gang with membrane cable gland
0 696 52L					Box 1 gang with PG16 cable gland on the top
0 696 56L	0 696 86L	0 696 28L			Box 1 gang with ISO20 cable gland on the top
0 698 46L					Box 1 gang with 2 ISO20 cable gland on the top
0 696 68L	0 698 66L	0 696 10L			Box 2 gangs vertical with 2 ISO20 cable gland on the top
0 695 96L					Membrane cable gland 1 entry
0 695 99L					Membrane cable gland 2 entries
0 696 65L					Coupling cable gland
0 696 48L					PG16 cable gland 1 entry
0 696 50L					PG16 cable gland 2 entries
0 696 53L					PG16 cable gland accessories
0 696 60L	0 696 62L	0 696 63L			ISO20 cable gland 1 entry
0 696 70L	0 696 71L	0 969 73L			ISO20 cable gland 2 entries



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 17/02/2026

Signature:



ANNEX

References Grey	References White	References Anthracite	References Sand	References Other	Designation
0 695 98L					Set of 4 caps
0 696 81L	0 696 92L	0 696 06L	0 698 90L		Frame 1 gang
0 696 83L	0 696 94L	0 696 07L	0 698 53L		Frame 2 gangs
0 700 54		0 700 94			Frame 2 gangs
0 696 87L	0 696 98L	0 696 08L			Frame 3 gangs
0 700 90		0 700 95			Frame 3 gangs
0 696 82L	0 696 93L	0 696 09L			Frame 1 gang with claws
0 695 79L		0 698 45L			Mosaic / Arteor adaptator with smoked flap lockable
0 919 45					Security tool
0 695 80L	0 696 95L	0 698 80L	0 698 38L		Mosaic / Arteor adaptator with smoked flap
0 695 84L	0 696 84L	0 698 30L			Mosaic / Arteor adaptator with flap
0 695 82L					Mosaic / Arteor adaptator without flap
				0 700 76L	2 rapido claws for renovation depth 40mm + spacer



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 17/02/2026

Signature



ANNEX

CLASSIFICATION

Standard Sheet:	V (cee 7)
Rated current (A)	16A
Rated voltage (V)	250V
Degree of protection	IP55
Provision for earthing	With earthing contact
Method of connecting the cable	Rewirable
Type of terminals	Screw-type screwless (rigid and flexible) Screw-type
socket-outlets	
Multiple socket-outlets	
Number of socket-outlets	16A
Degree of protection against electric shock	Increased protection
Existence of shutters	With shutters
Method of application - mounting	Surface – type flush-type
Method of installation	Design A



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 17/02/2026

Signature:

