

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Fixed socket-outlet

Name and address of the applicant

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
- FRANCE

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
- FRANCE

Name and address of the factory

See Annex

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

16 A, 250 V~

Trademark (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

SOLIROC series
References: 0 778 31, 0 778 32, 0 778 33

Additional information (if necessary may also be reported on page 2)

 Additional Information on page 2


A sample of the product was tested and found to be in conformity with

IEC 60884-1:2002(ed.3) +A1:2006 +A2:2013

As shown in the Test Report Ref. No. which forms part of this Certificate

118896-637230A1, 136736-675846A, 146030-698308,
146030-698308A

This CB Test Certificate is issued by the National Certification Body

LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr

Date: 23/11/2017

Signature: **Jean-François BRUEL**
Certification Officer

ANNEX

Name and address of the factories:**LEGRAND FRANCE**

128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX – FRANCE

LEGRAND FRANCE ISERE

Place du Breuil, 38680 PONT EN ROYANS - FRANCE

BTICINO S.P.A VARESE

VIALE L.BORRI 231 ; 21100 VARESE - ITALY

ERP ELBROMPLAST

Calea Vidrighin, Stan n° 13A ; 300571 TIMISOARA - ROMANIA


References, ratings and main characteristics

Type reference	References	Function	Characteristics	IP	IK	Specificity
PFA1	0 778 31	2P+T	16 A, 250 V~	55	10	With cover
	0 778 32	2P+T	16 A, 250 V~	40	10	Without cover
	0 778 33	2P+T	16 A, 250 V~	55	10	With keyed cover

Standard sheet	I (NF C 61-314) / V (CEE7)
Rated current (A)	16A
Rated voltage (V)	250V~
Degree of protection	See table above
Provision of earthing	with earthing contact
Method of connecting the cable	rewirable
Type des bornes	Screwless (rigid and flexible)
Degree of protection against electric shock	Normal protection
Existence of shutters	With shutters
method of application - mounting	Flush-type Surface-type with box 0 778 90 or 0 778 92
method of installation	design A



LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr



Date: 23/11/2017


Signature: **Jean-François BRUEL**
Certification Officer

ANNEX**Accessories**

References	Designation
0 802 51	Frame 1 gang
0 802 61	Frame 1 gang with short claws
0 802 52	Frame 2 gang
0 802 53	Frame 3 gang
0 778 51	Cover plate 1 gang
0 778 52	Cover plate 2 gang horizontal or vertical centres 71 mm
0 778 53	Cover plate 3 gang horizontal or vertical centres 71 mm
0 778 85	Foam joint cover plate 1 gang
0 778 86	Foam joint cover plate 2 gang
0 778 87	Foam joint cover plate 3 gang
0 778 90	Surface-type box 1 gang
0 778 92	Surface-type box 2 gang
0 778 96	Spare Cap



LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr



Date: 23/11/2017

Signature: **Jean-François BRUEL**
Certification Officer