



Ref. Certif. No.

FR_719413

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switches for household and similar fixed electrical installations

Switches for fixed installation

Name and address of the applicant

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD
A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST.
NASHIK 422113 MAHARASHTRA - INDIA

Name and address of the manufacturer

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD
A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST.
NASHIK 422113 MAHARASHTRA - INDIA

Name and address of the factory

Note: When more than one factory, please report on page 2

☒ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60669-1:2017

As shown in the Test Report Ref. No. which forms part of this Certificate

ADQW-ESH-P23120536

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 26/07/2024



LABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 15.745.984 €
RCS Nanterre B 408 363 174
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES

Signature:

Julien GAUTHIER
Certification Officer

ANNEX

Name and address of the factories:

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD

A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. NASHIK - 422113, MAHARASHTRA - INDIA

LEGRAND

AVENUE DU PARC ALATA - 60550 VERNEUIL EN HALATTE - FRANCE

RAIS HASSAN SAADI Logistics Dubai

Jebel Ali Free Zone, P.O. Box 7 Dubai - United Arab Emirates

LEGRAND FRANCE

128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY, 87045 LIMOGES CEDEX - FRANCE

Legrand Intelligent Electrical (Huizhou) Co., Ltd.

Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou 516001, Guangdong - CHINA

References, ratings and main characteristics:

All the commercial references listed below may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ... In this case, the products are technically the same.

Model list

CLASSIC references					
	White	Titanium	Black		
Type reference	Commercial ref	Commercial ref	Commercial ref	Module	Specificities
A028981AA	AC21116	/	/	1	red color of Rocker
	AC21101MW	AC21101MT	AC21101MB		
	AC21102MW	AC21102MT	AC21102MB		
	AC21118MW	AC21118MT	AC21118MB		with pilot light


Characteristics of appliance	
Pattern number	1
Contact opening (gap)	normal gap
Protection of degree	IP20
Method of actuating	rocker
Method of mounting	flush type
Method of installation	design A
Type fo terminals	screw type
Rated current (A) or (AX)	16AX
Rated voltage (V)	250V~



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE

33 avenue du Général Leclerc

92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr

Signature: **Julien GAUTHIER**
Certification Officer

Date: 26/07/2024

ANNEX

Accessories	
Pilot light	
Commercial ref	Designation
A180	230V red
A184	230V red

Frame

Commercial ref	Designation
A1402	1G 1 AND 2M BRITISH STD FRAME
A1403	1G 1 AND 2M BS FRAME W/ EARTH
A1404	1G 3M HORIZO/VERTICAL BS FRAME
A1408	2G 3M BS FRAME
A1409	2G 2 X 2M BS FRAME
A1406	3M IT/FR/SCH FRAME
A1407	6M IT/FR/SCH FRAME
A1400	1M PANEL MOUNTING SUPPORT
A1401	2M PANEL MOUNTING SUPPORT
A1405	4M FR/SCH FRAME


Blank

Commercial ref			Designation
Matt White	Matt Titanium	Matt Black	
AC150MW	AC150MT	AC150MB	1 BLANK MODULE
AC153MW	AC153MT	AC153MB	2 BLANK MODULES
AC1501MW	AC1501MT	AC1501MB	1G BS BLANKING PLATE
AC1502MW	AC1502MT	AC1502MB	2G BS BLANKING PLATE



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 26/07/2024



Signature: Julien GAUTHIER
Certification Officer

ANNEX

Cover plates


Commercial ref									Designation
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium	
AC110 0MW	AC1 100 MT	AC11 00MB	AC110 0FW	AC1100 FB	AC1100D A	AC1100B S	AC1100 NB	AC1100S A	1G 1M BS PLATE
AC110 1MW	AC1 101 MT	AC11 01MB	AC110 1FW	AC1101 FB	AC1101D A	AC1101B S	AC1101 NB	AC1101S A	1M ITALIAN/US PLATE
AC110 2MW	AC1 102 MT	AC11 02MB	AC110 2FW	AC1102 FB	AC1102D A	AC1102B S	AC1102 NB	AC1102S A	1G 2M BS PLATE
AC110 3MW	AC1 103 MT	AC11 03MB	AC110 3FW	AC1103 FB	AC1103D A	AC1103B S	AC1103 NB	AC1103S A	2M ITALIAN/US PLATE
AC110 4MW	AC1 104 MT	AC11 04MB	AC110 4FW	AC1104 FB	AC1104D A	AC1104B S	AC1104 NB	AC1104S A	1G 3M BS HORIZ/VERT PLATE
AC110 5MW	AC1 105 MT	AC11 05MB	AC110 5FW	AC1105 FB	AC1105D A	AC1105B S	AC1105 NB	AC1105S A	3M BS PLATE FOR 2G BOX
AC110 7MW	AC1 107 MT	AC11 07MB	AC110 7FW	AC1107 FB	AC1107D A	AC1107B S	AC1107 NB	AC1107S A	3M IT/US PLATE
AC110 8MW	AC1 108 MT	AC11 08MB	AC110 8FW	AC1108 FB	AC1108D A	AC1108B S	AC1108 NB	AC1108S A	2 X 2M BS PLATE
AC111 0MW	AC1 110 MT	AC11 10MB	AC111 0FW	AC1110 FB	AC1110D A	AC1110B S	AC1110 NB	AC1110S A	4M IT/FR/SCH PLATE
AC111 1MW	AC1 111 MT	AC11 11MB	AC111 1FW	AC1111 FB	AC1111D A	AC1111B S	AC1111 NB	AC1111S A	6M IT/FR/SCH PLATE
AC120 0MW	AC1 200 MT	AC12 00MB	AC120 0FW	AC1200 FB	AC1200D A	AC1200B S	AC1200 NB	AC1200S A	1M PLATE+FRAME
AC120 1MW	AC1 201 MT	AC12 01MB	AC120 1FW	AC1201 FB	AC1201D A	AC1201B S	AC1201 NB	AC1201S A	2M PLATE+FRAME
AC120 2MW	AC1 202 MT	AC12 02MB	AC120 2FW	AC1202 FB	AC1202D A	AC1202B S	AC1202 NB	AC1202S A	3M PLATE+FRAME
AC120 3MW	AC1 203 MT	AC12 03MB	AC120 3FW	AC1203 FB	AC1203D A	AC1203B S	AC1203 NB	AC1203S A	4M PLATE+FRAME
AC120 4MW	AC1 204 MT	AC12 04MB	AC120 4FW	AC1204 FB	AC1204D A	AC1204B S	AC1204 NB	AC1204S A	6M BS PLATE+FRAME
AC120 5MW	AC1 205 MT	AC12 05MB	AC120 5FW	AC1205 FB	AC1205D A	AC1205B S	AC1205 NB	AC1205S A	6M PLATE+FRAME
AC120 6MW	AC1 206 MT	AC12 06MB	AC120 6FW	AC1206 FB	AC1206D A	AC1206B S	AC1206 NB	AC1206S A	8M PLATE+FRAME



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr

Date: 26/07/2024




Signature: **Julien GAUTHIER**
Certification Officer

ANNEX

Commercial ref									Designation
Matt White	Matt Titanium m	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium m	
AC12 07M W	AC120 7MT	AC12 07MB	AC120 7FW	AC1207 FB	AC1207D A	AC1207B S	AC1207 NB	AC1207S A	8M PLATE+FRAME
AC12 08M W	AC120 8MT	AC12 08MB	AC120 8FW	AC1208 FB	AC1208D A	AC1208B S	AC1208 NB	AC1208S A	2 X 4M PLATE+FRAME
AC12 09M W	AC120 9MT	AC12 09MB	AC120 9FW	AC1209 FB	AC1209D A	AC1209B S	AC1209 NB	AC1209S A	2 X 6M BS PLATE+FRAME
AC12 10M W	AC121 0MT	AC12 10MB	AC121 0FW	AC1210 FB	AC1210D A	AC1210B S	AC1210 NB	AC1210S A	2 X 6M PLATE+FRAME
AC12 11M W	AC121 1MT	AC12 11MB	---	---	---	---	---	---	3 X 6M PLATE+FRAME
---	---	---	AB1100 FW	AB1100 FB	AB1100D A	AB1100B S	AB1100 NB	AB1100S A	4M HYBRID PLATE 2M + 2M SWITCH
---	---	---	AB1200 FW	AB1200 FB	AB1200D A	AB1200B S	AB1200 NB	AB1200S A	6M HYBRID PLATE 3M + 2M DIMMER
---	---	---	AB1201 FW	AB1201 FB	AB1201D A	AB1201B S	AB1201 NB	AB1201S A	6M HYBRID PLATE 3M + 2M SWITCH
---	---	---	AB1202 FW	AB1202 FB	AB1202D A	AB1202B S	AB1202 NB	AB1202S A	6M HYBRID PLATE+FRAM 3M+2M DIM
---	---	---	AB1203 FW	AB1203 FB	AB1203D A	AB1203B S	AB1203 NB	AB1203S A	6M HYBRID PLATE+FRAM 3M +2M SW
---	---	---	AB1204 FW	AB1204 FB	AB1204D A	AB1204B S	AB1204 NB	AB1204S A	6M HYBRID PLATE 4M + 1M SWITCH
---	---	---	AB1205 FW	AB1205 FB	AB1205D A	AB1205B S	AB1205 NB	AB1205S A	6M HYBRID PLATE+FRAME 4M+1M SW
---	---	---	AB1206 FW	AB1206 FB	AB1206D A	AB1206B S	AB1206 NB	AB1206S A	8M HYBRID PLATE 5M +2M DIMMER
---	---	---	AB1207 FW	AB1207 FB	AB1207D A	AB1207B S	AB1207 NB	AB1207S A	8M HYBRID PLATE+FRAM 5M+2M DIM
AC11 18M W	AC111 8MT	AC11 18MB	AC111 8FW	AC1118 FB	AC1118D A	AC1118B S	AC1118 SA	AC1118N B	4X4 US PLATE FOR 2M
AC12 12M W	AC121 2MB	AC12 12MT	---	---	---	---	---	---	9M PLATE+FRAME
AC12 13M W	AC121 3MB	AC12 13MT	---	---	---	---	---	---	2 X 8M PLATE+FRAME
---	---	---	AB1208 FW	AB1208 FB	AB1208B S	AB1208D A	AB1208 NB	AB1208S A	4M HYBRID PLATE+FRAME 2M + 2M SWITCH



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr



Signature: *Julien GAUTHIER*
Certification Officer

Date: 26/07/2024


ANNEX

Pattern number	1
Contact opening	normal gap
Protection degree	IP20
Method of actuating	rocker
Method of mounting	flush-type
Method of installation	design A
Type of terminals	screw-type (rigid and flexible)
Flexible cable outlet	without
Ratings	16AX 250V~
Color	White, Titanium, Black



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 26/07/2024



Signature: **Julien GAUTHIER**
Certification Officer