

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Shaver transformers and shaver supply units
Name and address of the applicant	LEGRAND FRANCE 128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY 87045 LIMOGES CEDEX FRANCE
Name and address of the manufacturer	LEGRAND FRANCE 128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY 87045 LIMOGES CEDEX FRANCE
Name and address of the factory	Legrand Intelligent Electrical (Huizhou) Co., Ltd. Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone Huizhou Guangdong - CHINA
Note: When more than one factory, please report on page 2	<input type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Annex
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	/
Model / Type Ref.	Series : MALLIA References : see annex
Additional information (if necessary may also be reported on page 2)	Supersedes CBTC FR_629874/M1 dated 26/01/2017. Addition of product references, change of factory <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61558-1:2005 +A1:2009(ed.2) IEC 61558-2-5:2010(ed. 2)
As shown in the Test Report Ref. No. which forms part of this Certificate	171741-762891 Version : 01

This CB Test Certificate is issued by the National Certification Body




LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr

Date: 09/06/2021



LABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 15.745.984 €
RCS Nanterre B 408 363 174
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES

Signature:  **Julien Gauthier**
Certification Officer

ANNEX

References, ratings and main characteristics:

Reference	Rated voltage		Other information
	supply	output	
2 811 35	230 V~	120/230 V~	White complete
2 811 35MW	230 V~	120/230 V~	Matt White
2 811 35MG	230 V~	120/230 V~	Matt Grey
2 811 35MB	230 V~	120/230 V~	Matt Black
2 811 35DS	230 V~	120/230 V~	Dark Silver
2 811 35CH	230 V~	120/230 V~	Champagne
2 811 35DB	230 V~	120/230 V~	Dark Bronze
2 811 35BA	230 V~	120/230 V~	Brushed Aluminium
2 811 35BB	230 V~	120/230 V~	Brushed Black
2 821 35	230 V~	120/230 V~	Matt Black without plate
2 831 35	230 V~	120/230 V~	Silver without plate
2 833 35	230 V~	120/230 V~	Pearl without plate
2 835 35	230 V~	120/230 V~	Dark silver without plate
2 839 35	230 V~	120/230 V~	Champagne without plate

Frequency	50 / 60 Hz
Supply	230 V~
Output	120 / 230 V
Power output	20 VA
Class	I
Short-circuit protection	Non-inherently short-circuit proof
Degree of protection	IP24
Mobility	Stationary
Time of operation	Continuous
Intended use	Associated for specific use
Rated maximum ambient temperature	25°C
Windings	Class A
Output connection	Socket
Terminals (Supply)	Screwless

Cover Plate (2x1 gang)	
Reference	Other information
2 819 01	White
2 819 06	Silver
2 819 11	Champagne
2 819 51	Pearl
2 819 56	Dark silver
2 819 61	Brass
2 819 66	Bronze
2 819 71	Matt black
2 819 76	Copper
2 819 79	Metal BSS
2 819 83	Metal gold
2 819 87	Metal PSS
2 819 91	Metal Lacquered black



LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr

Date: 09/06/2021



LABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 15.745.984 €
RCS Nanterre B 408 363 174
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES

Signature: *Julien Gauthier*
Certification Officer