



Ref. Certif. No.

ES1642-M3

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME**

CB TEST CERTIFICATE

Product

LED LUMINAIRES FOR EMERGENCY LIGHTING

Name and address of the applicant

LEGRAND GROUP ESPAÑA, S.L.
CL HIERRO, 56
28850 TORREJON DE ARDOZ (Madrid - Spain)

Name and address of the manufacturer

SAME AS ABOVE

Name and address of the factory

SAME AS ABOVE

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark (if any)

LEGRAND

Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

661611; 662613

Additional information (if necessary may also be reported on page 2)

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60598-1:2014
IEC 60598-2-22:2014


As shown in the Test Report Ref. No. which forms part of this Certificate

2016120783B1-M2

This CB Test Certificate is issued by the National Certification Body

AENOR INTERNACIONAL S.A.U.
CI Génova, 6
ES-28004 MADRID (SPAIN)

Date: 2018-02-27

Signature: 
Rafael GARCÍA MEIRO
Chief Executive Officer

ANNEX TO CB CERTIFICATE N° ES1642-M3

CERTIFIED REFERENCES AND THEIR MAIN RATINGS

Product: LED LUMINAIRES FOR EMERGENCY LIGHTING

Trade Mark: LEGRAND

Type reference	N° lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information
661611	LED 2 x 1 W	90 lm - 3 h	3,6 V 1,5 Ah NiCd 3 cells	Non maintained; Remote rest
662613	LED 4 x 1 W	350 lm - 2 h	4,8 V 2,0 Ah NiMH 4 cells	Maintained, possible non maintained; Remote rest

Rated voltage and frequency

230 V~; 50/60 Hz

IP degree of protection

IP 42; IK 07

Power supply connection means

Terminals

Classif. per holding surface material

Suitable for normally flammable surfaces

Protection against electric shocks (class)

Class II

General data

Electronic protection. URA-21