



Ref. Certif. No.

FR_702193/A1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Multiple cord extension set

Name and address of the applicant

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

NINGBO BANMEN ELECTRIC APPLIANCE CO., LTD
East Industrial Zone, Guanhaiwei Cixi City, 315314 ZHEJIANG
PROVINCE - CHINA

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

16 A, 250 V~, Max. 3680 W

See Annex

Trademark (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

694810, 694811

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_702193 dated 23/01/2018 (Update of the license for plug A14)

 Additional Information on page 2


A sample of the product was tested and found to be in conformity with

IEC 60884-1:2002+A1:2006 +A2:2013
IEC 60884-2-7:2011+A1:2013

As shown in the Test Report Ref. No. which forms part of this Certificate

BAN-17NO0049ACSC-1, BAN-17NO0049ACSC-2

This CB Test Certificate is issued by the National Certification Body

LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.frLABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 15 746 004 €
RCS Nanterre 4408 363 174
33 Avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES

Date: 18/05/2018

Signature: **Jean-François BRUEL**
Certification Officer

ANNEX

REFERENCES AND MAIN CHARACTERISTICS

Reference	Number of socket	With USB	With CBE	Colour of enclosure
694810	3	Yes	Yes	White
694811				Black

CLASSIFICATION

standard Sheet:	Standard sheet III (cee 7)
rated current (A)	16 A
rated load (W)	Max. 3680 W
rated voltage (V)	250 V~
household voltage (V)	230 V~
degree of protection	IP20
provision for earthing	with earthing contact
method of connecting the cable	non-rewirable
type of connections	soldered –other
colour	White, Black
socket-outlets	
multiple socket-outlets	
number of socket-outlets	16 A : 3
degree of protection against electric shock	normal protection
existence of shutters	with shutters
method of application - mounting	portable type
plugs:	
class of equipment	I

Components	Type / Reference	Manufacturer	Conformity
Plug	A14	Legrand	LCIE (FR_558589/M1)
Cable	HO5VV-F 3x1,5mm ²	Legrand	VDE (40017697)
USB	Built-in	Legrand	LCIE test report No. BAN-17NO0281VTSC
CBE	SS-006	Approach	*Test report No. 1711990020

*Test report issued by Zhejiang Fangyuan Test Group Co., Ltd (CNAS registration No. L0116)



LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr



Date: 18/05/2018

Signature: **Jean-François BRUEL**
Certification Officer