

IEC**IECEE**

®

TM

Ref. Certif. No.

FR_712119

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Intermediate adaptor

Name and address of the applicant

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the factory

BTICINO SPA
4 VIA LUCIANO MANARE
22036 ERBA
ITALY

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

Type ZLS 36
References: 0 648 40

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_707062 dated 22/10/2019.
Addition of product references
Change of factory Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2002 +A1:2006 +A2:2013
IEC 60884-2-5:2017

As shown in the Test Report Ref. No. which forms part of this Certificate

171369-762175

This CB Test Certificate is issued by the National Certification Body

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 11/08/2021

Signature: **Gilles LEMOINER**
Certification Officer

ANNEX

Mechanisms

Type reference	References	Nominal characteristics	Pattern	contact opening
ZLS36	0 648 40 5 742 54	16A 240V~	2 P+E	micro

Characteristics of appliances

Standard Sheet:	III CEE7 (Socket-outlet) and VII CEE7 (Plug)
Degree of protection	IP20
Protection for earthing	with earth contact
Degree of protection against the electric shocks	Normal protection
Presence of shutters	with shutters
Method of mounting	Portable-type
Pattern number	1
Method of actuating	Push button or other internal influences

Rated current (A) - rated load (VA or W) : for 240 V~

300 W halogen lamps
 60 W LED or 10 lamps
 60 W fluorescent compact lamps
 300 VA feromagnetic transformers for ELV halogen lamps
 300 VA electronic transformers for ELV halogen lamps

Minimum current (A) - minimum load (VA or W) :	5 W
Rated voltage (V)	240 V
Rated frequency (Hz)	50/60 Hz



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 11/08/2021



Signature: Gilles LEMOINIER
 Certification Officer