



Ref. Certif. No.

ES1961

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

FLUORESCENT LUMINAIRE FOR EMERGENCY LIGHTING

Name and address of the applicant

LEGRAND GROUP ESPAÑA, S.L.
CL HIERRO, 56
28850 TORREJON DE ARDOZ (Madrid - Spain)

Name and address of the manufacturer

LEGRAND FRANCE LAGORD
ZA DES GREFFIÈRES; 1, RUE EUGÈNE FREYSSINET
F17140 LAGORD (France)

Name and address of the factory

SAME AS ABOVE

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark (if any)

LEGRAND

Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

661512; 661521; 661523; 661525; 661533

Additional information (if necessary may also be reported on page 2)

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60598-1:2014
IEC 60598-2-22:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

2017060342B1

This CB Test Certificate is issued by the National Certification Body

AENOR INTERNACIONAL S.A.U.
CI Génova, 6
ES-28004 MADRID (SPAIN)

Date: 2018-02-01

Signature: Rafael GARCÍA MEIRO
Chief Executive Officer

ANNEX TO CB CERTIFICATE N° ES1961

CERTIFIED REFERENCES AND THEIR MAIN RATINGS

Product: FLUORESCENT LUMINAIRE FOR EMERGENCY LIGHTING

Trade Mark: LEGRAND

Type reference	No. lamps x rated wattage	Type of lamps and lampholder	Rated lumen output	Rated duration	Additional information
661512	Lamp 2 x 8 W	Fluorescent; Lampholder G5	200 Lm	1 h	Combined non maintained; Ni-Cd 1,5 Ah. B66 (8W)
661521	Lamp 1 x 8 W	Fluorescent; Lampholder G5	100 Lm	1 h	Non maintained; Ni-Cd 1,5 Ah. B66 (8W)
661523	Lamp 1 x 8 W	Fluorescent; Lampholder G5	250 Lm	1 h	Non maintained; Ni-Cd 1,5 Ah. B66 (8W)
661525	Lamp 1 x 11 W	Fluorescent; Lampholder 2G7	450 Lm	1 h	Non maintained; Ni-Cd 1,5 Ah. B66 (11W)
661533	Lamp 1 x 8 W	Fluorescent; Lampholder G5	260 Lm	2 h	Non maintained; Ni-Cd 1,5 Ah. B66 (8W)

Rated voltage and frequency

230 V~; 50/60 Hz

IP degree of protection

IP 66; IK 08

Means for power connection

Terminals

Classif. per holding surface material

Suitable for normally flammable surfaces

Protection against electric shocks (class)

Class II