



Ref. Certif. No.

FR\_712212

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Electronic switch  
Fan control

Name and address of the applicant

**Legrand Intelligent Electrical (Huizhou) Co., Ltd.**  
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech  
Industrial Development Zone, Huizhou, Guangdong - CHINA

Name and address of the manufacturer

**Legrand Intelligent Electrical (Huizhou) Co., Ltd.**  
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech  
Industrial Development Zone, Huizhou, Guangdong - CHINA

Name and address of the factory

**Legrand Intelligent Electrical (Huizhou) Co., Ltd.**  
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech  
Industrial Development Zone, Huizhou, Guangdong - CHINA

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

Max 100W, 200-240V~  
See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60669-1:2017  
IEC 60669-2-1:2002+A1:2008+A2:2015

As shown in the Test Report Ref. No. which forms part of this Certificate

ARLI-ESH-P21030020

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE  
33 avenue du Général Leclerc  
92260 Fontenay-aux-Roses, FRANCE  
[www.lcie.fr](http://www.lcie.fr)

Date: 31/08/2021



LABORATOIRE CENTRAL DES  
INDUSTRIES ELECTRIQUES  
S.A.S au capital de 15.745.984 €  
RCS Nanterre B 408 363 174  
33 avenue du Général Leclerc  
F - 92266 FONTENAY AUX ROSES

Signature:   
Julien Gauthier  
Certification Officer

## ANNEX

References, ratings and main characteristics:


REFERENCE	COLOR
281082MW	Matt white
281082MWSG	Matt white
281082MG	Matt grey
281082MB	Matt black
281082MBSG	Matt black
281082DS	Dark silver
281082DSSG	Dark silver
281082CH	Champagne
281082CHSG	Champagne
281082DB	Dark bronze
281082DBSG	Dark bronze
281082BA	Brushed aluminium
281082BASG	Brushed aluminium
281082BB	Brushed black
281082BBSG	Brushed black
281082BC	Brushed champagne

*281082 series with xxSG means with earthing terminal.*



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE  
33 avenue du Général Leclerc  
92260 Fontenay-aux-Roses, FRANCE  
[www.lcie.fr](http://www.lcie.fr)

Date: 31/08/2021



Signature: *Julien Gauthier*  
Julien Gauthier  
Certification Officer


## ANNEX

Type of electronic switch	Speed controller (rotary switch)
Pattern number	1
Contact opening (gap)	micro-gap
Protection degree	IP20
Method of actuating	rotary
Method of mounting	flush-type
Method of installation	design A -
Type of terminals	screw-type
Flexible cable outlet	without
Rated current (A) - Rated load (VA or W)	100W
Kind of load controlled	motors
Rated voltage (V)	200-240V
Rated frequency (Hz)	50/60



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE  
 33 avenue du Général Leclerc  
 92260 Fontenay-aux-Roses, FRANCE  
[www.lcie.fr](http://www.lcie.fr)

Date: 31/08/2021



Signature:  **Julien Gauthier**  
 Certification Officer