



Ref. Certif. No.

FR_719420/A1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switches for household and similar fixed electrical installations

Switches for fixed installation

Name and address of the applicant

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD
A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST.
NASHIK - 422113, MAHARASHTRA - INDIA

Name and address of the manufacturer

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD
A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST.
NASHIK - 422113, MAHARASHTRA - INDIA

Name and address of the factory

Note: When more than one factory, please report on page 2

☒ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_719420 dated 05/08/2024.
Editorial correction

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60669-1:2017

As shown in the Test Report Ref. No. which forms part of this Certificate


ADQW-ESH-P24020369


This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 19/08/2024

Signature: 
Certification Officer



ANNEX

Name and address of the factories:**NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD**

A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. NASHIK - 422113, MAHARASHTRA - INDIA

LEGRAND

AVENUE DU PARC ALATA - 60550 VERNEUIL EN HALATTE - FRANCE

RAIS HASSAN SAADI Logistics Dubai

Jebel Ali Free Zone, P.O. Box 7 Dubai - United Arab Emirates

LEGRAND FRANCE


128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY, 87045 LIMOGES CEDEX - FRANCE

Legrand Intelligent Electrical (Huizhou) Co., Ltd.

Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou 516001, Guangdong - CHINA



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE

33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCEwww.lcie.frSignature: Jérôme REYSSON
Certification Officer

Date: 19/08/2024

ANNEX

References, ratings and main characteristics:

All the commercial references listed below may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ... In this case, the products are technically the same.

CLASSIC references					
	White	Titanium	Black		
Type reference	Commercial ref	Commercial ref	Commercial ref	Module	Specificities
A028989AA	AC21103MW	AC21103MT	AC21103MB	2	

Characteristics of appliance	
Pattern number	1
Contact opening (gap)	normal gap
Protection of degree	IP20
Method of actuating	Rocker
Method of mounting	flush type
Method of installation	design A
Type fo terminals	screw type
Rated current (A) or (AX)	16AX
Rated voltage (V)	250V~

Frame


Commercial ref	Designation
A1402	1G 1 AND 2M BRITISH STD FRAME
A1403	1G 1 AND 2M BS FRAME W/ EARTH
A1404	1G 3M HORIZO/VERTICAL BS FRAME
A1408	2G 3M BS FRAME
A1409	2G 2 X 2M BS FRAME
A1406	3M IT/FR/SCH FRAME
A1407	6M IT/FR/SCH FRAME
A1401	2M PANEL MOUNTING SUPPORT
A1405	4M FR/SCH FRAME

Blank

Commercial ref			Designation
Matt White	Matt Titanium	Matt Black	
AC150MW	AC150MT	AC150MB	1 BLANK MODULE
AC153MW	AC153MT	AC153MB	2 BLANK MODULES
AC1501MW	AC1501MT	AC1501MB	1G BS BLANKING PLATE
AC1502MW	AC1502MT	AC1502MB	2G BS BLANKING PLATE



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr



Signature: Jérôme REYSSON
Certification Officer

Date: 19/08/2024

ANNEX

Cover plates

Commercial ref									
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium	Designation
AC110 4MW	AC110 4MT	AC11 04MB	AC110 4FW	AC110 4FB	AC1104 DA	AC1104BS	AC11 04NB	AC1104 SA	1G 3M BS HORIZ/VERT PLATE
AC110 5MW	AC110 5MT	AC11 05MB	AC110 5FW	AC110 5FB	AC1105 DA	AC1105BS	AC11 05NB	AC1105 SA	3M BS PLATE FOR 2G BOX
AC110 7MW	AC110 7MT	AC11 07MB	AC110 7FW	AC110 7FB	AC1107 DA	AC1107BS	AC11 07NB	AC1107 SA	3M IT/US PLATE
AC110 8MW	AC110 8MT	AC11 08MB	AC110 8FW	AC110 8FB	AC1108 DA	AC1108BS	AC11 08NB	AC1108 SA	2 X 2M BS PLATE
AC111 0MW	AC111 0MT	AC11 10MB	AC111 0FW	AC111 0FB	AC1110 DA	AC1110BS	AC11 10NB	AC1110 SA	4M IT/FR/SCH PLATE
AC111 1MW	AC111 1MT	AC11 11MB	AC111 1FW	AC111 1FB	AC1111 DA	AC1111BS	AC11 11NB	AC1111 SA	6M IT/FR/SCH PLATE
AC120 1MW	AC120 1MT	AC12 01MB	AC120 1FW	AC120 1FB	AC1201 DA	AC1201BS	AC12 01NB	AC1201 SA	2M PLATE+FRAME
AC120 2MW	AC120 2MT	AC12 02MB	AC120 2FW	AC120 2FB	AC1202 DA	AC1202BS	AC12 02NB	AC1202 SA	3M PLATE+FRAME
AC120 3MW	AC120 3MT	AC12 03MB	AC120 3FW	AC120 3FB	AC1203 DA	AC1203BS	AC12 03NB	AC1203 SA	4M PLATE+FRAME
AC120 4MW	AC120 4MT	AC12 04MB	AC120 4FW	AC120 4FB	AC1204 DA	AC1204BS	AC12 04NB	AC1204 SA	6M BS PLATE+FRAME
AC120 5MW	AC120 5MT	AC12 05MB	AC120 5FW	AC120 5FB	AC1205 DA	AC1205BS	AC12 05NB	AC1205 SA	6M PLATE+FRAME
AC120 6MW	AC120 6MT	AC12 06MB	AC120 6FW	AC120 6FB	AC1206 DA	AC1206BS	AC12 06NB	AC1206 SA	8M PLATE+FRAME
AC120 7MW	AC120 7MT	AC12 07MB	AC120 7FW	AC120 7FB	AC1207 DA	AC1207BS	AC12 07NB	AC1207 SA	8M PLATE+FRAME
AC120 8MW	AC120 8MT	AC12 08MB	AC120 8FW	AC120 8FB	AC1208 DA	AC1208BS	AC12 08NB	AC1208 SA	2 X 4M PLATE+FRAME
AC120 9MW	AC120 9MT	AC12 09MB	AC120 9FW	AC120 9FB	AC1209 DA	AC1209BS	AC12 09NB	AC1209 SA	2 X 6M BS PLATE+FRAME
AC121 0MW	AC121 0MT	AC12 10MB	AC121 0FW	AC121 0FB	AC1210 DA	AC1210BS	AC12 10NB	AC1210 SA	2 X 6M PLATE+FRAME
AC121 1MW	AC121 1MT	AC12 11MB	---	---	---	---	---	---	3 X 6M PLATE+FRAME
---	---	---	AB110 0FW	AB110 0FB	AB1100 DA	AB1100BS	AB11 00NB	AB1100 SA	4M HYBRID PLATE 2M + 2M SWITCH
---	---	---	AB120 0FW	AB120 0FB	AB1200 DA	AB1200BS	AB12 00NB	AB1200 SA	6M HYBRID PLATE 3M + 2M DIMMER
---	---	---	AB120 1FW	AB120 1FB	AB1201 DA	AB1201BS	AB12 01NB	AB1201 SA	6M HYBRID PLATE 3M + 2M SWITCH
---	---	---	AB120 2FW	AB120 2FB	AB1202 DA	AB1202BS	AB12 02NB	AB1202 SA	6M HYBRID PLATE+FRAM 3M+2M DIM
---	---	---	AB120 3FW	AB120 3FB	AB1203 DA	AB1203BS	AB12 03NB	AB1203 SA	6M HYBRID PLATE+FRAM 3M +2M SW
---	---	---	AB120 4FW	AB120 4FB	AB1204 DA	AB1204BS	AB12 04NB	AB1204 SA	6M HYBRID PLATE 4M + 1M SWITCH



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 19/08/2024



Signature: Jérôme REYSSON
Certification Officer

ANNEX


Cover plates

Commercial ref									
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium	Designation
---	---	---	AB120 5FW	AB120 5FB	AB1205 DA	AB1205BS	AB12 05NB	AB1205 SA	6M HYBRID PLATE+FRAME 4M+1M SW
---	---	---	AB120 6FW	AB120 6FB	AB1206 DA	AB1206BS	AB12 06NB	AB1206 SA	8M HYBRID PLATE 5M +2M DIMMER
---	---	---	AB120 7FW	AB120 7FB	AB1207 DA	AB1207BS	AB12 07NB	AB1207 SA	8M HYBRID PLATE+FRAM 5M+2M DIM
AC111 8MW	AC111 8MT	AC11 18MB	AC111 8FW	AC111 8FB	AC1118 DA	AC1118BS	AC11 18SA	AC1118 NB	4X4 US PLATE FOR 2M
AC121 2MW	AC121 2MB	AC12 12MT	---	---	---	---	---	---	9M PLATE+FRAME
AC121 3MW	AC121 3MB	AC12 13MT	---	---	---	---	---	---	2 X 8M PLATE+FRAME
---	---	---	AB120 8FW	AB120 8FB	AB1208 BS	AB1208DA	AB12 08NB	AB1208 SA	4M HYBRID PLATE+FRAME 2M + 2M SWITCH

Pattern number	1
Contact opening	normal gap
Protection degree	IP20
Method of actuating	Rocker
Method of mounting	flush-type
Method of installation	design A
Type of terminals	screw-type (rigid and flexible)
Flexible cable outlet	without
Ratings	16AX 250V~
Color	White, Titanium, Black



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr



Signature: Jérôme REYSSON
Certification Officer

Date: 19/08/2024