



ENEC Certification Body registered under ID # 01. For further information, please consult [www.enec.com](http://www.enec.com)

# LICENCE

to use the European Mark



**Licence Nr.** ENEC/001219

**Under the conditions given in the following pages of this document, the licence to use the ENEC Mark in conjunction with the suffix 01, as shown above, has been issued to:**

LEGRAND GROUP ESPAÑA, S.L.  
HIERRO, 56  
28850 TORREJON DE ARDOZ (Madrid – España / Spain)

**For the product(s):**

LED luminaires for emergency lighting

**Trade name(s):**

LEGRAND

**Complying with the following European Standards:**

EN IEC 60598-1:2021;  
EN 60598-2-22:2014; EN 60598-2-22:2014/A1:2020;  
EN 62262:2002

**Date:** 2023-01-05

**Signature:**

A handwritten signature in blue ink, appearing to read "Rafael García", written over a horizontal line.

**Name:** Rafael García

**Position:** Chief Executive Officer

This licence has been issued under the presumption and conditional on the fact that the licensee holds all necessary legal rights with regard to the product presented for testing and certification.

AENOR INTERNACIONAL, S.A.U.  
Cl Génova, 6  
28004 MADRID (Spain)

## CERTIFICATE OF THE ENEC EUROPEAN MARK

|                                                  |                                                                                               |
|--------------------------------------------------|-----------------------------------------------------------------------------------------------|
| Type of Product                                  | LED LUMINAIRES FOR EMERGENCY LIGHTING                                                         |
| r1) Certificate n°                               | ENEC/001219                                                                                   |
| r2) Date of the Certificate                      | 2023-01-05                                                                                    |
| r3) report n°                                    | 2022010001B1-M1                                                                               |
| r4) Name and address of the licensee             | LEGRAND GROUP ESPAÑA, S.L.<br>HIERRO, 56<br>28850 TORREJON DE ARDOZ (Madrid - España / Spain) |
| r5) Address of the factory                       | HIERRO, 56<br>28850 TORREJON DE ARDOZ (Madrid - España / Spain)                               |
| r6) European Standard                            | EN IEC 60598-1:2021;<br>EN 60598-2-22:2014; EN 60598-2-22:2014/A1:2020;<br>EN 62262:2002      |
| r7) Type reference                               | See above for details                                                                         |
| r8) Trade Mark                                   | LEGRAND                                                                                       |
| r9) Rated voltage and frequency                  | 230 V~; 50/60 Hz                                                                              |
| r10) N° lamps x rated power, type and lampholder | See above for details                                                                         |
| r11) IP degree of protection                     | IP42; IK 07                                                                                   |
| r12) Power supply connection means               | Bornes Terminals                                                                              |
| r13) Classif. per holding surface material       | Apta para superficies normalmente inflamables Suitable for normally flammable surfaces        |
| r14) Protection against electric shocks (class)  | Clase II Class II                                                                             |
| r15) Rated lumen output and duration             | See above for details                                                                         |
| r16) Battery features                            | See above for details                                                                         |
| r17) Additional information                      | See above for details                                                                         |
| r18) General data                                | See above for details                                                                         |
| Date of expiry: 2025-04-30                       |                                                                                               |

## CERTIFICATE OF THE ENEC EUROPEAN MARK

| Type reference | Nº lamps x rated power, type and lampholder | Rated lumen output and duration | Battery features  | Additional information                                                        | General data                                                       |
|----------------|---------------------------------------------|---------------------------------|-------------------|-------------------------------------------------------------------------------|--------------------------------------------------------------------|
| 660000         | 2 x 0,25W; módulo module LED                | 50 lm - 1 h                     | NiCd 3,6 V 0,7 Ah | No permanente<br>Non maintained;<br>Puesta en reposo<br>remota Remote<br>rest | Protección<br>electrónica<br>Electronic<br>Protection; URA<br>NEXT |
| 660001         | 2 x 0,25W; módulo module LED                | 70 lm - 1 h                     | NiCd 3,6 V 0,7 Ah | No permanente<br>Non maintained;<br>Puesta en reposo<br>remota Remote<br>rest | Protección<br>electrónica<br>Electronic<br>Protection; URA<br>NEXT |
| 660002         | 2 x 0,25W; módulo module LED                | 100 lm - 1 h                    | NiCd 3,6 V 0,7 Ah | No permanente<br>Non maintained;<br>Puesta en reposo<br>remota Remote<br>rest | Protección<br>electrónica<br>Electronic<br>Protection; URA<br>NEXT |
| 660003         | 4 x 0,25W; módulo module LED                | 160 lm - 1 h                    | NiCd 3,6 V 1,1 Ah | No permanente<br>Non maintained;<br>Puesta en reposo<br>remota Remote<br>rest | Protección<br>electrónica<br>Electronic<br>Protection; URA<br>NEXT |
| 660004         | 4 x 0,25W; módulo module LED                | 200 lm - 1 h                    | NiCd 3,6 V 1,1 Ah | No permanente<br>Non maintained;<br>Puesta en reposo<br>remota Remote<br>rest | Protección<br>electrónica<br>Electronic<br>Protection; URA<br>NEXT |
| 660013         | 4 x 0,25W; módulo module LED                | 160 h - 1 h                     | NiCd 3,6 V 1,1 Ah | No permanente<br>Non maintained;<br>Puesta en reposo<br>remota Remote<br>rest | Protección<br>electrónica<br>Electronic<br>Protection; URA<br>NEXT |
| 660022         | 4 x 0,25W; módulo module LED                | 100 lm - 1 h                    | NiCd 3,6 V 0,7 Ah | Permanente<br>Maintained;<br>Puesta en reposo<br>remota Remote<br>test        | Protección<br>electrónica<br>Electronic<br>Protection; URA<br>NEXT |
| 660024         | 4 x 0,25W; módulo module LED                | 200 lm - 1 h                    | NiCd 3,6 V 1,1 Ah | Permanente<br>Maintained;<br>Puesta en reposo<br>remota Remote<br>test        | Protección<br>electrónica<br>Electronic<br>Protection; URA<br>NEXT |

## CERTIFICATE OF THE ENEC EUROPEAN MARK

| Type reference | Nº lamps x rated power, type and lampholder | Rated lumen output and duration | Battery features  | Additional information                                                                                      | General data                                                        |
|----------------|---------------------------------------------|---------------------------------|-------------------|-------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------|
| 660051         | 2 x 0,25W; módulo module LED                | 70 lm - 1 h                     | NiCd 3,6 V 0,7 Ah | No permanente<br>Non maintained;<br>Puesta en reposo<br>remota Remote<br>rest                               | Protección electrónica<br>Electronic<br>Protection; X-<br>LIGHT 180 |
| 660052         | 2 x 0,25W; módulo module LED                | 100 lm - 1 h                    | NiCd 3,6 V 0,7 Ah | No permanente<br>Non maintained;<br>Puesta en reposo<br>remota Remote<br>rest                               | Protección electrónica<br>Electronic<br>Protection; X-<br>LIGHT 180 |
| 660053         | 2 x 0,25W; módulo module LED                | 100 lm - 1 h                    | NiCd 3,6 V 0,7 Ah | No permanente<br>Non maintained;<br>Puesta en reposo<br>remota Remote<br>rest                               | Protección electrónica<br>Electronic<br>Protection; X-<br>LIGHT 180 |
| 660054         | 4 x 0,25W; módulo module LED                | 200 lm - 1 h                    | NiCd 3,6 V 1,1 Ah | No permanente<br>Non maintained;<br>Puesta en reposo<br>remota Remote<br>rest                               | Protección electrónica<br>Electronic<br>Protection; X-<br>LIGHT 180 |
| 660059         | 4 x 0,25W; módulo module LED                | 100 lm - 3 h                    | NiCd 3,6 V 1,1 Ah | No permanente<br>Non maintained;<br>Puesta en reposo<br>remota Remote<br>rest                               | Protección electrónica<br>Electronic<br>Protection; X-<br>LIGHT 180 |
| 660060         | 4 x 0,25W; módulo module LED                | 100 lm - 3 h                    | NiCd 3,6 V 1,1 Ah | No permanente<br>Non maintained;<br>Puesta en reposo<br>remota Remote<br>rest                               | Protección electrónica<br>Electronic<br>Protection; X-<br>LIGHT 180 |
| 660071         | 4 x 0,25W; módulo module LED                | 70 lm - 1 h                     | NiCd 3,6 V 0,7 Ah | No permanente/Perm<br>anente Non<br>maintained/Maint<br>ained;<br>Puesta en reposo<br>remota Remote<br>rest | Protección electrónica<br>Electronic<br>Protection; X-<br>LIGHT 180 |

## CERTIFICATE OF THE ENEC EUROPEAN MARK

| Type reference | Nº lamps x rated power, type and lampholder | Rated lumen output and duration | Battery features  | Additional information                                                                  | General data                                                    |
|----------------|---------------------------------------------|---------------------------------|-------------------|-----------------------------------------------------------------------------------------|-----------------------------------------------------------------|
| 660072         | 4 x 0,25W; módulo module LED                | 100 lm - 1 h                    | NiCd 3,6 V 0,7 Ah | No permanente/Permanente Non maintained/Maintained; Puesta en reposo remota Remote rest | Protección electrónica Electronic Protection; X-LIGHT 180       |
| 660074         | 4 x 0,25W; módulo module LED                | 200 lm - 1 h                    | NiCd 3,6 V 1,1 Ah | No permanente/Permanente Non maintained/Maintained; Puesta en reposo remota Remote rest | Protección electrónica Electronic Protection; X-LIGHT 180       |
| 660100         | 4 x 0,25W; módulo module LED                | 50 lm - 1 h                     | NiMh 3,6 V 0,5 Ah | No permanente Non maintained; Puesta en reposo remota Remote rest                       | Protección electrónica Electronic Protection; URA NEXT Autotest |
| 660101         | 4 x 0,25W; módulo module LED                | 70 lm - 1 h                     | NiMh 3,6 V 0,5 Ah | No permanente Non maintained; Puesta en reposo remota Remote rest                       | Protección electrónica Electronic Protection; URA NEXT Autotest |
| 660102         | 4 x 0,25W; módulo module LED                | 100 lm - 1 h                    | NiMh 3,6 V 0,5 Ah | No permanente Non maintained; Puesta en reposo remota Remote rest                       | Protección electrónica Electronic Protection; URA NEXT Autotest |
| 660104         | 4 x 0,25W; módulo module LED                | 200 lm - 1 h                    | NiCd 3,6 V 1,1 Ah | No permanente Non maintained; Puesta en reposo remota Remote rest                       | Protección electrónica Electronic Protection; URA NEXT Autotest |

## CERTIFICATE OF THE ENEC EUROPEAN MARK

| Type reference | Nº lamps x rated power, type and lampholder | Rated lumen output and duration | Battery features  | Additional information                                                        | General data                                                                       |
|----------------|---------------------------------------------|---------------------------------|-------------------|-------------------------------------------------------------------------------|------------------------------------------------------------------------------------|
| 660154         | 4 x 0,25W; módulo module LED                | 200 lm - 1 h                    | NiCd 3,6 V 1,1 Ah | No permanente<br>Non maintained;<br>Puesta en reposo<br>remota Remote<br>rest | Protección<br>electrónica<br>Electronic<br>Protection; X-<br>LIGHT 180<br>Autotest |