Ref. Certif. No.

FR_705599

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	**Fixed socket-outlet**
Name and address of the applicant	**LEGRAND FRANCE** 128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY 87045 LIMOGES CEDEX FRANCE
Name and address of the manufacturer	**LEGRAND FRANCE** 128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY 87045 LIMOGES CEDEX FRANCE
Name and address of the factory	See Annex
Note: *When more than one factory, please report on page 2*	☒ Additional Information on page 2
Ratings and principal characteristics	16A, 250V~ See Annex
Trademark (if any)	legrand
Customer's Testing Facility (CTF) Stage used	/
Model / Type Ref.	Series : SALBEI References : See Annex
Additional information (if necessary may also be reported on page 2)	Supersedes CBTC FR_675844/M1 dated 04/12/2018. Addition of product references ☒ Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60884-1:2002(ed.3) +A1:2006 +A2:2013
As shown in the Test Report Ref. No. which forms part of this Certificate	136736-675863A, 102525-603992B, 136736-675859A, 102525-603992A1, 154428-718586B, 131584-664986A, 158526-730187D, 158526-730187G

This CB Test Certificate is issued by the National Certification Body

LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES
S.A.S au capital de 15.745.984 €
RCS Nanterre B 408 363 174
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES

Date: 29/04/2019

Signature: **Julien GAUTHIER**
Certification Officer

ANNEX

Name and address of the factories:

EMB ELECTRICAL INDUSTRIES SAE
SECOND INDUSTRIAL ZONE - SADAT CITY AREA 18 - P.O. BOX 14
32958 MENOFIA – EGYPT

LEGRAND ELEKTRIK SANAYI A.S
GOSB GEBZE ORGANIZE SANAYI BOLGESI - IHSAN DEDE CADDESI N°112
41480 GEBZE KOCAELI - TURKEY

LEGRAND MAGYARORSZAG VILLAMOSSAGI RENDSZEREK ZRt
IPARTELEPI UT 14 PF 10
6600 SZENTES - HUNGARY

ANNEX (Continued)

REFERENCES, RATINGS AND MAIN CHARACTERISTICS

Mechanisms

type reference	References									Type	Terminals	Shutters	Standard sheet	specifity
	White with claws	Ivory with claws	Aluminium with claws	Anthracite with claws	Champagne with claws	Matt Gold with claw	Pink with claw	Smoked Grey with claw	White Pearl with claw					
767x14 NSS21	7 671 14	7 674 14	7 672 14	7 673 14	7 675 14	7 676 14	7 677 14	7 678 14	7 679 14	2P+E	st	without	III (CEE7)	
NSS21	3 977 09	3 977 39	3 977 69	3 978 29	3 978 18	3 973 65	3 973 99	3 974 48	3 974 87	2P+E	st	without	III (CEE7)	7 67x 14 + 7 673 A1
7 67x 15 NSS22	7 671 15	7 674 15	7 672 15	7 673 15	7 675 15	7 676 15	7 677 15	7 678 15	7 679 15	2P+E	st	with	III (CEE7)	
NSS22	3 977 10	3 977 40	3 977 70	3 978 30	3 978 19	3 973 66	3 974 00	3 974 49	3 974 88	2P+E	st	with	III (CEE7)	7 67x 15 + 7 673 A1
7 67x 18 NSS22	7 671 18	7 674 18	7 672 18	7 673 18	7 675 18	7 676 18	7 677 18	7 678 18	7 679 18	2P+E	st	with	III (CEE7)	with lid
NSS22	3 977 12	3 977 42	3 977 72	3 978 32	3 978 35	3 973 67	3 974 02	3 974 50	3 974 89	2P+E	st	with	III (CEE7)	7 67x 18 + 7 673 A1
7 67x 16 NSSG2	7 671 16	7 674 16	7 672 16	7 673 16	7 675 16	7 676 16	7 677 16	7 678 16	7 679 16	2 x 2P+E	st	with	III (CEE7)	1 gang
NSSG2	3 977 11	3 977 41	3 977 71	3 978 31	3 978 34	3 973 68	3 974 03	3 974 52	3 974 91	2 x 2P+E	st	with	III (CEE7)	7 67x 16 + 7 673 A1
7 67x 17 NSF22	7 671 17	7 674 17	7 672 17	7 673 17	7 675 17	7 676 17	7 677 17	7 678 17	7 679 17	2P+E	st	with	V (CEE7)	
NSF22	7 671 19									2P+E	st	with	V (CEE7)	red cover
LXX09	7 671 88	7 674 88	7 672 88							2P+E	slt	with	III (CEE7)	With USB type C

Slt : screwless terminals
St : screw type terminals

ANNEX (Continued)

Characteristics

Standard sheet	III / V (CEE7) see table
rated current (A)	16A
rated voltage (V)	250V~
degree of protection	IP20
provision for earthing	with earthing contact
method of connecting the cable	rewirable
degree of protection against electric shock	normal protection
method of application - mounting	flush type Surface type with surface boxes
method of installation	design A
terminals	screw type screwless

Component	Model	Manufacturer	Conformity
USB type C	LXX09	LEGRAND	TR LCIE 158526-730181

ANNEX (Continued)

Accessories

surface boxes

Type references	References	Designation
7 67x 47	7 671 47	1 gang white
	7 672 47	1 gang aluminium
	7 673 47	1 gang anthracite
	7 674 47	1 gang ivory
	7 675 47	1 gang champagne
	7 676 47	1 gang matt gold
	7 677 47	1 gang pink
	7 678 47	1 gang smoked grey
	7 679 47	1 gang white pearl
7 67x 48	7 671 48	2 gang white
	7 672 48	2 gang aluminium
	7 673 48	2 gang anthracite
	7 674 48	2 gang ivory
	7 675 48	2 gang champagne
	7 676 48	2 gang matt gold
	7 677 48	2 gang pink
	7 678 48	2 gang smoked grey
	7 679 48	2 gang white pearl

Mosaïc adaptor with claws

Type references	References	Designation
7 67x 89	7 671 89	White
	7 672 89	Aluminium
	7 673 89	Anthracite
	7 674 89	Ivory
	7 675 89	Champagne
	7 676 89	Matt Gold
	7 677 89	Pink
	7 678 89	Smoked Grey
	7 679 89	White pearl

ANNEX (End)

Cover plates

Type references	Designation	References										
		White	Ivory	Aluminium	Anthracite	Champagne	Bright Wood	White Pearl	Matt Gold	Pink	Smoked Grey	Dark Wood
7 673 x1	1 gang	7 673 31	7 673 41	7 673 51	7 673 61	7 673 71	7 673 81	-	-	-	-	-
7 673 x2	2 gang	7 673 32	7 673 42	7 673 52	7 673 62	7 673 72	7 673 82	-	-	-	-	-
7 673 x3	3 gang	7 673 33	7 673 43	7 673 53	7 673 63	7 673 73	7 673 83	-	-	-	-	-
7 673 x4	4 gang	7 673 34	7 673 44	7 673 54	7 674 64	7 673 74	7 673 84	-	-	-	-	-
7 673 x5	5 gang	7 673 35	7 673 45	7 673 55	7 673 65	7 673 75	7 673 85	-	-	-	-	-
7 67x 91	6 gang	7 671 91	7 674 91	7 672 91	7 673 91	7 675 91		7 679 91	7 676 91	7 677 91	7 678 91	
7 67x 92	6 gang	-	-	-	-	-	7 673 92	-	-	-	-	-
7 673 x6	1 gang IP44 IK07	7 673 36	7 673 46	-	-	-	-	-	-	-	-	-
7 675 x1	1 gang	-	-	-	-	-	-	7 675 41	7 675 61	7 675 71	7 675 51	7 675 31
7 675 x2	2 gang	-	-	-	-	-	-	7 675 42	7 675 62	7 675 72	7 675 52	7 675 32
7 675 x3	3 gang	-	-	-	-	-	-	7 675 43	7 675 63	7 675 73	7 675 53	7 675 33
7 675 x4	4 gang	-	-	-	-	-	-	7 675 44	7 675 64	7 675 74	7 675 54	7 675 34
7 675 x5	5 gang	-	-	-	-	-	-	7 675 45	7 675 65	7 675 75	7 675 55	7 675 35
7 67x 90	1 gang label holder	7 671 90	7 674 90	7 672 90	7 673 90	7 675 90	-	7 679 90	7 676 90	7 677 90	7 678 90	-