



Ref. Certif. No.

SE-118495

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switched socket-outlet (flush type)

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, Huizhou, Guangdong, China

Name and address of the manufacturer

LEGRAND FRANCE
128, Avenue du Maréchal de Lattre de Tassigny 87045
Limoges Cedex, France

Name and address of the factory

☒ Additional Information on page 2

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

13A 250V~, IP20

Trademark / Brand (if any)

See page 2

Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

See page 2

Additional information (if necessary may also be reported on page 2)

☒ Additional Information on page 2-3

A sample of the product was tested and found to be in conformity with

IEC 60884-2-3:2006
IEC 60884-1:2022

As shown in the Test Report Ref. No. which forms part of this Certificate

2512B0188SHA-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamnsgatan 43
Box 1103
SE-164 22 Kista, Sweden

Date: 22 January, 2026

intertek

Signature:

Hyden Li

Factories

1. Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, China

2. Novateur Electrical & Digital Systems Private Limited
A-2, MIDC Industrial Area, Malegaon Village, Sinnar, Nashik Maharashtra, 422113, India

Model / Type Ref.

281117MW, 281117MG, 281117MB, 281117DS, 281117CH, 281117DB, 281117BA, 281117BB, 281119MW, 281119MG, 281119MB, 281119DS, 281119CH, 281119DB, 281119BA, 281119BB, 6 176 48, 6 177 48, 6 178 48, 6 180 48, 282487, 282487-C, 282487-C1, 282487-C2, 282487-C3, 8 380 82, MEC32040WH, MEC32040SL, MEC32040CH, MEC32040BL, MEC32040RG

Trademark



or tenby for 8 380 82



for other models

Additional information

Flush type, Class I, rewirable, with screw-type terminals, with 2 gang switched socket outlets comply with type G (configuration of BS 1363-2), with shutters, with one double pole switch for each socket-outlet, with plastic cover plate or plastic lining combined with metal sheet cover plate, with or without metal frame, with or without indicator lamp.

Total 31 models:

6 176 48: with white front cover and plastic white cover plate, without metal frame.
6 177 48: with dark front cover and plastic dark cover plate, without metal frame.
6 178 48: with ivory front cover and plastic ivory cover plate, without metal frame.
281117MW: with dark front cover and matt white plastic cover plate, with metal frame.
281117MG: with dark front cover and matt grey plastic cover plate, with metal frame.
281117MB: with dark front cover and matt black plastic cover plate, with metal frame.
281117DS: with dark front cover and dark silver plastic cover plate, with metal frame.
281117CH: with dark front cover and champagne plastic cover plate, with metal frame.
281117DB: with dark front cover and dark bronze plastic cover plate, with metal frame.
281117BA: with dark front cover and plastic lining combined with brushed aluminium metal sheet cover plate, with metal frame.
281117BB: with dark front cover and plastic lining combined with brushed black metal sheet cover plate, with metal frame.
281119MW: with dark front cover and matt white plastic cover plate, with metal frame, with indicator lamp.
281119MG: with dark front cover and matt grey plastic cover plate, with metal frame, with indicator lamp.
281119MB: with dark front cover and matt black plastic cover plate, with metal frame, with indicator lamp.
281119DS: with dark front cover and dark silver plastic cover plate, with metal frame, with indicator lamp.
281119CH: with dark front cover and champagne plastic cover plate, with metal frame, with indicator lamp.
281119DB: with dark front cover and dark bronze plastic cover plate, with metal frame, with indicator lamp.
281119BA: with dark front cover and plastic lining combined with brushed aluminium metal sheet cover plate, with metal frame, with indicator lamp.
281119BB: with dark front cover and plastic lining combined with brushed black metal sheet cover plate, with metal frame, with indicator lamp.
6 180 48 and 8 380 82: similar to 6 176 48 except the shape of cover plate.

Date: 22 January, 2026

Signature:



282487: similar to 281117MW except the shape of cover plate and without metal frame.
282487-C: similar to 282487 except the cover plate with matt black color.
282487-C1: similar to 282487 except the cover plate with rose gold color.
282487-C2: similar to 282487 except the cover plate with champagne color.
282487-C3: similar to 282487 except the cover plate with dark silver color.
MEC32040WH: with white plastic front cover and white plastic cover plate, without metal frame.
MEC32040SL: with white plastic front cover and silver plastic cover plate, without metal frame.
MEC32040CH: with white plastic front cover and champagne plastic cover plate, without metal frame.
MEC32040BL: with white plastic front cover and black plastic cover plate, without metal frame.
MEC32040RG: with white plastic front cover and rose gold plastic cover plate, without metal frame.

Date: 22 January, 2026

Signature:

A handwritten signature in blue ink, appearing to be 'unfllc', is written over the 'Signature:' label.