



Ref. Certif. No.

SE-85949

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Dimmer switch for fixed installation

Name and address of the applicant

Legrand (Beijing) Electrical Co. Ltd
No. 4 Chaoqian Road, Changping Kejiyuanqu, Beijing,
CHINA

Name and address of the manufacturer

Same as applicant

Name and address of the factory

Note: When more than one factory, please report on page 2

Same as applicant

Ratings and principal characteristics

See page 2

Trademark (if any)

legrand

Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

281086, 283086, 283286, 283486, 283886, 282086, 617035,
617235, 617335, 617435

Additional information (if necessary may also be reported on page 2)

See page 2

A sample of the product was tested and found to be in conformity with

IEC 60669-1:1998+A1 + A2
IEC 60669-2-1:2002+A1+A2

As shown in the Test Report Ref. No. which forms part of this Certificate

160702527SHA-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Box 1103
SE-164 22 Kista, Sweden
Int +46 8 750 00 00

Date: 9 February 2017

Intertek

Signature:

Gary Hu

Ratings and principal characteristics

100-240V~ 50/60Hz ε IP20

1) at 100-200V~ rating voltage:

5-150W incandescent lamps,

5-150VA electronic step-down converter for extra low-voltage incandescent lamps

5-150VA Externally ballasted fluorescent lamps

5-37W dimmable CFL

2) at 200-240V~ rating voltage:

5-300W incandescent lamps,

5-300VA electronic step-down converter for extra low-voltage incandescent lamps

5-300VA Externally ballasted fluorescent lamps

5-75W dimmable CFL

Date: 9 February 2017

Signature: 