



Ref. Certif. No.

FR_722770/M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Multiple cord extension set

Name and address of the applicant

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

JIANDE HUNLEE ELECTRICAL APPLIANCE CO., LTD
CHENGNAN INDUSTRIAL PARK, MEICHENG TOWN IN
JIANDE CITY, HANGZHOU, ZHEJIANG - CHINA

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)

legrand

Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_722770 dated 10/10/2025.
Addition of components

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022

As shown in the Test Report Ref. No. which forms part of this Certificate

ABND-ESH-P25091432

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 05/12/2025

Signature

LABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 15 745 081 €
Julien CAUTHIER
33 avenue du Général Leclerc
92260 FONTENAY-AUX-ROSES

ANNEX

References, ratings and main characteristics:

| Model | Reference | Number of socket-outlets | Cable cross-section area & cable length (H05VV-F) | With USB | With Switch | Color of enclosure |
|----------|-----------|----------------------------|---|----------|-------------|--------------------|
| RNHS102 | 0 496 20 | 3 | 3G1,0mm ² /1,5m | N | Y | WHITE/ GREY |
| | 0 496 21 | 3 | 3G1,5mm ² /1,5m | N | Y | WHITE/ GREY |
| | 0 496 22 | 3 | 3G1,0mm ² /1,5m | N | Y | BLACK |
| | 0 496 23 | 3 | 3G1,5mm ² /1,5m | N | Y | BLACK |
| | 0 496 24 | 4 | 3G1,0 mm ² /1,5m | N | Y | WHITE/ GREY |
| | 0 496 25 | 4 | 3G1,5mm ² /1,5m | N | Y | WHITE/ GREY |
| | 0 496 26 | 4 | 3G1,0mm ² /1,5m | N | Y | BLACK |
| | 0 496 27 | 4 | 3G1,5mm ² /1,5m | N | Y | BLACK |
| | 0 496 28 | 5 | 3G1,0mm ² /1,5m | N | Y | WHITE/ GREY |
| | 0 496 29 | 5 | 3G1,5mm ² /1,5m | N | Y | WHITE/ GREY |
| | 0 496 30 | 5 | 3G1,0mm ² /1,5m | N | Y | BLACK |
| | 0 496 31 | 5 | 3G1,5mm ² /1,5m | N | Y | BLACK |
| | 0 496 32 | 3 | 3G1,5mm ² /3,0m | N | Y | WHITE/ GREY |
| | 0 496 33 | 3 | 3G1,5mm ² /3,0m | N | Y | BLACK |
| | 0 496 34 | 4 | 3G1,5mm ² /3,0m | N | Y | WHITE/ GREY |
| | 0 496 35 | 4 | 3G1,5mm ² /3,0m | N | Y | BLACK |
| | 0 496 36 | 5 | 3G1,5mm ² /3,0m | N | Y | WHITE/ GREY |
| 0 496 37 | 5 | 3G1,5mm ² /3,0m | N | Y | BLACK | |
| RNHS102U | 0 496 52 | 3 | 3G1,0mm ² /1,5m | Y | Y | WHITE/ GREY |
| | 0 496 53 | 3 | 3G1,5mm ² /1,5m | Y | Y | WHITE/ GREY |
| | 0 496 54 | 3 | 3G1,0mm ² /1,5m | Y | Y | BLACK |
| | 0 496 55 | 3 | 3G1,5mm ² /1,5m | Y | Y | BLACK |
| | 0 496 56 | 4 | 3G1,0mm ² /1,5m | Y | Y | WHITE/ GREY |
| | 0 496 57 | 4 | 3G1,5mm ² /1,5m | Y | Y | WHITE/ GREY |
| | 0 496 58 | 4 | 3G1,0mm ² /1,5m | Y | Y | BLACK |
| | 0 496 59 | 4 | 3G1,5mm ² /1,5m | Y | Y | BLACK |



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 05/12/2025

Signature



LABORATOIRE CENTRAL DES
 INDUSTRIES ELECTRIQUES
 S.A.S au capital de 15 745 984 €
Julien GAUTHIER
 33 avenue du Général Leclerc
 92260 FONTENAY-AUX-ROSES

ANNEX

| | |
|---|---|
| standard Sheet: | Standard sheet V of CEE 7 (socket-outlet) / Standard sheet VII of CEE 7 (Plug) |
| rated current (A) | 16 A |
| rated load (W) | 3680 W |
| rated voltage (V) | 250 V~ |
| household voltage (V) | 230 V~ |
| degree of protection | ordinary |
| provision for earthing | with earthing contact (Solid earthing pin) |
| method of connecting the cable | non-rewirable |
| type of terminals | - |
| type of connections | Soldered / welded / other (riveted) |
| colour | See tabel above |
| socket-outlets | |
| multiple socket-outlets | 16 A : 3, 4, 5 |
| number of socket-outlets | |
| degree of protection against electric shock | normal protection |
| existence of shutters | with shutters |
| method of application - mounting | portable type |
| method of installation | - |
| plugs: | |
| class of equipment | I |
| entry of cable | lateral |

| type of components | manufacturer | Certification |
|--------------------|----------------------------------|--|
| Plug | Legrand France | NF012_3672 VDE 40055967 |
| Cable | Legrand France | VDE 40017697 |
| Switch | Cixi City Minghe Xinghua | SE-S-2200608 |
| | HUIYANG ZING EAR INDUSTRY CO LTD | ENEC-05522 |
| USB charger | Legrand France | Intertek test report No. 250423061SZN-001 |



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 05/12/2025

Signature:


 LABORATOIRE CENTRAL DES
 INDUSTRIES ELECTRIQUES
 S.A. - Siège social - 15 745 894 6
 33 avenue du Général Leclerc
 92260 FONTENAY-AUX-ROSES
Julien GAUTHIER
 Certification Officer