

AENOR

ENEC Certification Body registered under ID # 01. For further information, please consult www.enec.com

LICENCE

to use the European Mark



Licence Nr. ENEC/001271

Under the conditions given in the following pages of this document, the licence to use the ENEC Mark in conjunction with the suffix 01, as shown above, has been issued to:

LEGRAND GROUP ESPAÑA, S.L.
HIERRO, 56
28850 TORREJON DE ARDOZ (Madrid – España / Spain)

For the product(s):

LED luminaires for emergency lighting

Trade name(s):

LEGRAND

Complying with the following European Standards:

EN IEC 60598-1:2021; EN IEC 60598-1:2021/A11:2022;
EN IEC 60598-2-22:2022;
EN 62262:2002;
EN 62262:2002/A1:2021

A handwritten signature in blue ink, appearing to read 'Rafael García'.

Date: 2024-10-04

Signature:

Name: Rafael García
Position: Chief Executive Officer

This licence has been issued under the presumption and conditional on the fact that the licensee holds all necessary legal rights with regard to the product presented for testing and certification.

AENOR CONFÍA, S.A.U.
Cl Génova, 6
28004 MADRID (Spain)

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type of Product	LED LUMINAIRES FOR EMERGENCY LIGHTING
r1) Certificate n°	ENEC/001271
r2) Date of the Certificate	2024-10-04
r3) report n°	2023100536B1
r4) Name and address of the licensee	LEGRAND GROUP ESPAÑA, S.L. HIERRO, 56 28850 TORREJON DE ARDOZ (Madrid - España / Spain)
r5) Address of the factory	ZA DES GREFFIÈRES; 1, RUE EUGÈNE FREYSSINET F17140 LAGORD (Francia)
r6) European Standard	EN IEC 60598-1:2021; EN IEC 60598-1:2021/A11:2022; EN IEC 60598-2-22:2022 EN 62262:2002; EN 62262:2002/A1:2021
r7) Type reference	See above for details
r8) Trade Mark	LEGRAND
r9) Rated voltage and frequency	230 V~; 50/60 Hz
r10) N° lamps x rated power, type and lampholder	See above for details
r11) IP degree of protection	IP65, IK07
r12) Power supply connection means	Bornes Terminals
r13) Classif. per holding surface material	Apta para superficies normalmente inflamables Suitable for normally flammable surfaces
r14) Protection against electric shocks (class)	Clase II Class II
r15) Rated lumen output and duration	See above for details
r16) Battery features	LiFePO4 9,6 V - 3,2 Ah
r17) Additional information	No permanente Non maintained; Puesta en reposo remota Remote rest
r18) General data	See above for details

Date of expiry: 2029-10-04

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Nº lamps x rated power, type and lampholder	Rated lumen output and duration	General data
660460	2 x 2 W	1000 lm - 1h	Familia Series BAP; Autotest
660462	3 x 2 W	1500 lm - 1h	Familia Series BAP; Autotest
660463	3 x 2 W	2500 lm - 1h	Familia Series BAP; Autotest
660465	3 x 2 W	1500 lm - 2h	Familia Series BAP; Autotest
661460	2 x 2 W	1000 lm - 1h	Familia Series BAP; STD
661462	3 x 2 W	1500 lm - 1h	Familia Series BAP; STD
661463	3 x 2 W	2500 lm - 1h	Familia Series BAP; STD
662463	3 x 2 W	2500 lm - 1h	Familia Series BAP; STD