

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	HEBS Switches
Name and address of the applicant	LEGRAND FRANCE 128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY 87045 LIMOGES CEDEX FRANCE
Name and address of the manufacturer	LEGRAND FRANCE 128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY 87045 LIMOGES CEDEX FRANCE
Name and address of the factory	LEGRAND FRANCE 128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY 87045 LIMOGES CEDEX FRANCE
Note: When more than one factory, please report on page 2	<input type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Annex
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	/
Model / Type Ref.	Series : PLEXO References : See Annex
Additional information (if necessary may also be reported on page 2)	Supersedes CBTC FR_709166 dated 31/07/2020. Editorial correction <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60669-1:1998(ed.3) +A1:1999 +A2:2006 IEC 60669-2-1:2002(ed.4) +A1:2008 IEC 60669-2-5:2013
As shown in the Test Report Ref. No. which forms part of this Certificate	164951-746319A Ver. 01, SMT/AP08/H00154.1.1, SMT/AP08/H00155.1.1, SMT/AP08/H00155.2.1, 161191-736140B, 162469-739593B Ver 01, 164951-746319B, 155902-722432B, 156754-725057B, 60039319-539295

This CB Test Certificate is issued by the National Certification Body



LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr



LABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 15.745.984 €
RCS Nanterre B 408 363 174
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES

Signature: 
Julien Gauthier
Certification Officer

Date: 16/02/2021

ANNEX

Mechanisms

References	Colors	Nominal characteristics	Pattern	Specificity
0 697 94	Grey	3V	6	Remote switch
0 697 96	Grey	16A 100-240V~ 16A 250V~	1 2P+E	French standard
0 697 93	Grey	16A 100-240V~ 16A 250V~	1 2P+E	German standard

Characteristics of appliances

pattern number	see table
degree of protection	IP 55
method of mounting	Surface
method of installation	design A

Rated current (A) - rated load (VA or W) :
for 240V~


ZLS33 :

3680W cos φ 0,8

Minimum current (A) - minimum load (VA or W) :



LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr



Signature: *Julien Gauthier*
Julien Gauthier
Certification Officer

Date: 16/02/2021