

## IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

## CB TEST CERTIFICATE

## Product

Circuit-breakers for overcurrent protection for household and similar installations

## Name and address of the applicant

Legrand France SA  
128 Avenue du Marechal-de-Lattre de Tassigny,  
FR-87045 Limoges Cedex  
France

## Name and address of the manufacturer

bticino S.p.A.  
Viale Borri, 231  
21100 Varese (VA)  
Italy

## Name and address of the factory

*Note: When more than one factory, please report on page 2*

BTICINO S.p.A. – Legrand Group  
Via Dell'Industria, 22  
80059 – Torre del Greco (NA)  
Italy

[Additional information on page 2](#)

## Ratings and principal characteristics

1P (Ue = 230/400 V), 2P (Ue = 400 V), 3P (Ue = 400 V) or 4P (Ue = 400 V);  
50/60 Hz; Icn = 6000 A; curve B, C or D;  
In = 0.5, 1, 2, 3, 4, 6, 10, 13, 16, 20, 25, 32, 40, 50 or 63 A  
(see also pages 7 and 9 of Test Report No. PB23-0089287-01-00  
and/or Additional Sheet)

## Trademark / Brand (if any)

**legrand**

legrand

## Customer's Testing Facility (CTF) Stage used

CTF Stage 2

## Model / Type Ref.

DX<sup>3</sup> series (see also Additional Sheet)

## Additional information (if necessary may also be reported on page 2)

[Additional information on page 2](#)

## A sample of the product was tested and found to be in conformity with

IEC 60898-1:2015, IEC 60898-1:2015/AMD1:2019

## National differences:

EU Group Differences

## As shown in the Test Report Ref. No. which forms part of this Certificate

PB23-0089287-01-00 and from PB23-0089287-01-01 to PB23-0089287-01-63

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.  
Via Quintiliano 43  
Milano, 20138  
Italy



Date: 2023-09-21

Signature: Fabio Taormina

**Additional factory**

Legrand Low Voltage Electrical (Wuxi) Co., Ltd.  
No.88 Ximei Road, Xinwu District,  
Wuxi City, Jiangsu Province  
China

Branch Ulyanoskyi of Legrand LLC  
30th proezd Injenemyi, 5.1  
432072 Ulyanovsk  
Russian Federation

EMB Electrical Industries S.A.E.  
Sadat City Factory, 2nd Industrial Zone  
Monufya – 32958 Sadat City  
Egypt

Legrand India (Novateur electrical & Digital Systems Private Limited)  
D-4 MIDC Industrial Estate,  
Ajanta Road – Maharashtra,  
425003 Jalgaon  
India

Legrand Polska Sp. z.o.o.  
ul. Waryńskiego 20  
57-200 Ząbkowice Śląskie  
Poland

Legrand Elektrik Sanayi A.Ş.  
GÖSB Gebze Organize Sanayi Bolgesi  
Ihsan Dede Caddesi No. 112  
41480 Gebze KOCAELI  
Türkiye

Legrand Colombia S.A.  
Calle 65A #93-91, Bogotá  
Colombia

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.  
Via Quintiliano 43  
Milano, 20138  
Italy



Date: 2023-09-21

Signature: Fabio Taormina

**Type reference of the circuit-breakers DX<sup>3</sup> series (I<sub>cn</sub> = 6000 A)**

Curve	Rated current	Type reference			
		1P	2P	3P	4P
B	1 A	4074 25	4075 02	4075 54	4076 17
	2 A	4074 26	4075 03	4075 55	4076 18
	3 A	4074 27	4075 04	4075 56	4076 19
	4 A	4074 28	4075 05	4075 57	4076 20
	6 A	4074 29	4075 06	4075 58	4076 21
	10 A	4074 30	4075 07	4075 59	4076 22
	13 A	4074 31	4075 08	4075 60	4076 23
	16 A	4074 32	4075 09	4075 61	4076 24
	20 A	4074 33	4075 10	4075 62	4076 25
	25 A	4074 34	4075 11	4075 63	4076 26
	32 A	4074 35	4075 12	4075 64	4076 27
	40 A	4074 36	4075 13	4075 65	4076 28
	50 A	4074 37	4075 14	4075 66	4076 29
	63 A	4074 38	4075 15	4075 67	4076 30
C	1 A	4076 62	4077 92	4078 51	4079 20
	2 A	4076 63	4077 93	4078 52	4079 21
	3 A	4076 64	4077 94	4078 53	4079 22
	4 A	4076 65	4077 95	4078 54	4079 23
	6 A	4076 66	4077 96	4078 55	4079 24
	10 A	4076 68	4077 98	4078 57	4079 26
	13 A	4076 69	4077 99	4078 58	4079 27
	16 A	4076 70	4078 00	4078 59	4079 28
	20 A	4076 71	4078 01	4078 60	4079 29
	25 A	4076 72	4078 02	4078 61	4079 30
	32 A	4076 73	4078 03	4078 62	4079 31
	40 A	4076 74	4078 04	4078 63	4079 32
	50 A	4076 75	4078 05	4078 64	4079 33
	63 A	4076 76	4078 06	4078 65	4079 34
D	0,5 A	4079 62	4080 22	4080 80	—
	1 A	4079 63	4080 23	4080 81	—
	2 A	4079 64	4080 24	4080 82	—
	3 A	4079 65	4080 25	4080 83	—
	4 A	4079 66	4080 26	4080 84	—
	6 A	4079 67	4080 27	4080 85	4081 43
	10 A	4079 69	4080 29	4080 87	4081 45
	13 A	4079 70	4080 30	4080 88	4081 46
	16 A	4079 71	4080 31	4080 89	4081 47
	20 A	4079 72	4080 32	4080 90	4081 48
	25 A	4079 73	4080 33	4080 91	4081 49
	32 A	4079 74	4080 34	4080 92	4081 50
	40 A	4079 75	4080 35	4080 93	4081 51
	50 A	4079 76	4080 36	4080 94	4081 52
63 A	4079 77	4080 37	4080 95	4081 53	