



Ref. Certif. No.

**FR\_709925/M1**

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**

## CB TEST CERTIFICATE

Product

**Shaver transformers and shaver supply units**

Name and address of the applicant

**Legrand Intelligent Electrical (Huizhou) Co., Ltd.**  
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech  
Industrial Development Zone, Huizhou, 516001  
Guangdong - CHINA

Name and address of the manufacturer

**LEGRAND FRANCE**  
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY  
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

*Note: When more than one factory, please report on page 2*

☒ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)

- 1) legrand (for all model exclude 7 380 41)
- 2) tenby (for model 7 380 41 only)

Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

Series: SYNERGY  
References: See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR\_709925 dated 09/11/2020.  
Addition of product references  
Addition of components  
Change address of factory  
Change of licence holder and trademark

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 61558-1:2005 +A1:2009(ed.2)  
IEC 61558-2-5:2010(ed. 2)

As shown in the Test Report Ref. No. which forms part of this Certificate

ARLI-ESH-P24110875

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE  
33 avenue du Général Leclerc  
92260 Fontenay-aux-Roses, FRANCE  
[www.lcie.fr](http://www.lcie.fr)

Date: 11/06/2025

Signature:



## ANNEX

### Name and address of the factories:

#### **Legrand Intelligent Electrical (Huizhou) Co., Ltd.**

Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone  
Huizhou, 516001, Guangdong - CHINA

#### **LEGRAND ELECTRIC Ltd**

UNIT 12 N° 1 INDUSTRIALL ESTATE MEDOMSLEY ROAD CONSETT  
COUNTY DURHAM, DH8 6SR - UNITED KINGDOM

### References, ratings and main characteristics:

#### **Model list:**

Reference	Rated voltage		Color of enclosure
	Supply	Output	
7 300 90	230V	120/230V	White
8 320 90	230V	120/230V	Sleek design brushed stainless steel
8 322 90	230V	120/230V	Sleek design polished stainless steel
8 324 90	230V	120/230V	Sleek design glossy gold
8 330 90	230V	120/230V	Authentic brushed stainless steel
8 332 90	230V	120/230V	Authentic polished stainless steel
8 334 90	230V	120/230V	Authentic glossy gold
7 380 41	230V	120/230V	White

### **CLASSIFICATION**

Frequency	50 / 60 Hz
Supply	230 V~
Output	120 / 230 V
Power output	20 VA
Class	I
Short-circuit protection	Non-inherently short-circuit proof
Degree of protection	IP24
Mobility	Stationary
Time of operation	Continuous
Intended use	Associated for specific use
Rated maximum ambient temperature	25°C
Windings	Class A
Output connection	Socket
Terminals (Supply)	Screwless



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE

33 avenue du Général Leclerc  
92260 Fontenay-aux-Roses, FRANCE

[www.lcie.fr](http://www.lcie.fr)

Date: 11/06/2025

Signature: *Alien GAUTHIER*

