

Product Environmental Profile

RJ 45 SOCKET MOSAIC - CATEGORY 6A STP - 2 MOD & 1 MOD - WHITE



LEGRAND'S ENVIRONMENTAL COMMITMENTS

- Incorporate environmental management into our industrial sites**

Of all Legrand sites worldwide, over 85% are ISO 14001-certified (sites belonging to the Group for more than five years).

- Offer our customers environmentally friendly solutions**

Develop innovative solutions to help our customers design more energy efficient, better managed and more environmentally friendly installations.


- Involve the environment in product design and provide informations in compliance with ISO 14025**

Reduce the environmental impact of products over their whole life cycle.

Provide our customers with all relevant information (composition, consumption, end of life, etc.).



REFERENCE PRODUCT

Function	Connect a connection point for 10 years (reference life) with a 25 % utilization rate for a copper telecom accessory for a Tertiary LAN application.
Reference Product	
	Cat.Nos 0 765 76 - 0 802 51 - 0 788 02L
	RJ 45 SOCKET MOSAIC - CATEGORY 6A STP - 2 MODULES WHITE.

The company reserves the right to change specifications and designs without notice. All illustrations, descriptions, dimensions and weights in the document are for guidance and cannot be held binding on the company.



PRODUCTS CONCERNED

The environmental data is representative of the following products:

RJ 45 SOCKET 2M	RJ 45 SOCKET 1M	Blanking Plate 1M	Support	Plate 2M
0 765 76	0 765 73	0 777 70	0 802 51	0 788 02L

Product Environmental Profile

RJ 45 SOCKET MOSAIC - CATEGORY 6A STP - 2 MOD & 1 MOD - WHITE



■ CONSTITUENT MATERIALS

This Reference Product contains no substances prohibited by the regulations applicable at the time of its introduction to the market. It respects the restrictions on use of hazardous substances as defined in the RoHS directive 2011/65/EU amended by delegated directive (EU) 2015/863, and its amendment 2017/2102/EU.

Total weight of Reference Product		138 g (all packaging included)			
Plastics as % of weight		Metals as % of weight		Other as % of weight	
PC	12.4 %	Zamak	18.6 %	Electronic card	0.6 %
ABS	6.2 %	Steel	13.3 %		
PA	5.0 %	Copper alloys	0.7 %		
PET	2.0 %	Other metal	< 0.1 %		
PBT	1.0 %				
PE	0.4 %				
Various plastics	< 0.1 %				
Packaging as % of weight					
PP	0.4 %			Wood	25.3 %
PE	0.2 %			Paper	13.9 %
Total plastics	27.6 %	Total metals	32.6 %	Total others	39.8 %

Estimated recycled material content: 16 % by mass.



■ MANUFACTURE

This Reference Product comes from sites that have received ISO14001 certification.



■ DISTRIBUTION

Products are distributed from logistics centres located with a view to optimize transport efficiency. The Reference Product is therefore transported over an average distance of 780 km by road from our warehouse to the local point of distribution into the market Europe. Packaging is compliant with applicable regulation. At their end of life, its recyclability rate is 95 % (in % of packaging weight).



■ INSTALLATION

For the installation of the product, only standard tools are needed.



■ USE

Under normal conditions of use, this product requires no servicing, no maintenance or additional products.

Product Environmental Profile

RJ 45 SOCKET MOSAIC - CATEGORY 6A STP - 2 MOD & 1 MOD - WHITE



END OF LIFE

The product end of life factors are taken into account during the design phase. Dismantling and sorting of components or materials is made as easy as possible with a view to recycling or failing that, another form of reuse. This product falls within the scope of the WEEE directive (2012/19/EU). Therefore it must be processed through local WEEE recycling/recovery channels.

• **Extended producer responsibility:**

The sale of this product is subject to a contribution to eco-organisations in each country responsible for managing end of life products in the field of application of the European Waste Electronic and Electrical Equipment Directive.

• **Recyclability rate:**

Calculated using the method described in technical report IEC/TR 62635, the recyclability rate of the product is estimated at 97 %. This value is based on data collected from a technological channel operating on an industrial basis. It does not pre-validate the effective use of this channel for the end of life of this product.

Separated into:

- plastic materials (excluding packaging) : 26 %
- metal materials (excluding packaging) : 33 %
- other materials (excluding packaging) : 0 %
- packaging (all types of materials) : 38 %



ENVIRONMENTAL IMPACTS

The evaluation of environmental impacts examines the stages of the Reference Product life cycle: manufacturing, distribution, installation, use and end of life. It is representative from products marketed and used in Europe, in compliance with the local current standards.

For each phase, the following modelling elements were taken in account:

Manufacture	Materials and components of the product, all transport for the manufacturing, the packaging and the waste generated by the manufacturing.
Distribution	Transport between the last Group distribution centre and an average delivery point in the sales area.
Installation	The end of life of the packaging.
Use	<ul style="list-style-type: none"> • Product category: Socket RJ45 - PSR-0005-ed2-EN-2016 03 29 - 3.8.1.2. Copper Telecom accessories. • Use scenario: LAN tertiary, non continuous operation for 10 years, cat 6 for 25 % of the time. This time modeling is not requirement of minimum durability. • Energy model: Electricity Mix; Europe 27- 2008.
End of life	The default end of life scenario maximizing the environmental impacts.
Software and database used	EIME & database CODDE-2018-11

Product Environmental Profile

RJ 45 SOCKET MOSAIC - CATEGORY 6A STP - 2 MOD & 1 MOD - WHITE



SELECTION OF ENVIRONMENTAL IMPACTS

	Total for Life cycle		Raw material and manufacture		Distribution		Installation		Use		End of life	
	Value	Unit	Value	%	Value	%	Value	%	Value	%	Value	%
Global warming	8.93E-01	kgCO ₂ eq.	8.24E-01	92 %	5.37E-03	< 1 %	3.03E-03	< 1 %	5.29E-02	6 %	7.47E-03	< 1 %
Ozone depletion	3.76E-08	kgCFC-11 eq.	3.40E-08	90 %	1.09E-11	< 1 %	1.41E-11	< 1 %	3.44E-09	9 %	1.35E-10	< 1 %
Acidification of soils and water	1.61E-03	kgSO ₂ eq.	1.33E-03	82 %	2.41E-05	1 %	1.40E-05	< 1 %	2.21E-04	14 %	2.97E-05	2 %
Water eutrophication	1.21E-03	kg(PO ₄) ³⁻ eq.	1.14E-03	94 %	5.54E-06	< 1 %	8.53E-06	< 1 %	1.33E-05	1 %	4.04E-05	3 %
Photochemical ozone formation	1.88E-04	kgC ₂ H ₄ eq.	1.70E-04	91 %	1.71E-06	< 1 %	9.98E-07	< 1 %	1.21E-05	6 %	2.28E-06	1 %
Depletion of abiotic resources - elements	9.20E-05	kgSb eq.	9.20E-05	100 %	2.15E-10	< 1 %	1.28E-10	< 1 %	4.59E-09	< 1 %	4.16E-10	< 1 %
Total use of primary energy	1.63E+01	MJ	1.51E+01	92 %	7.59E-02	< 1 %	4.21E-02	< 1 %	1.06E+00	6 %	8.62E-02	< 1 %
Net use of fresh water	2.34E-01	m ³	4.19E-02	18 %	4.80E-07	< 1 %	6.11E-07	< 1 %	1.92E-01	82 %	4.77E-06	< 1 %
Depletion of abiotic resources - fossil fuels	8.97E+00	MJ	8.18E+00	91 %	7.54E-02	< 1 %	4.14E-02	< 1 %	6.00E-01	7 %	8.00E-02	< 1 %
Water pollution	1.35E+02	m ³	1.30E+02	97 %	8.83E-01	< 1 %	4.82E-01	< 1 %	2.18E+00	2 %	9.31E-01	< 1 %
Air pollution	1.60E+02	m ³	1.57E+02	98 %	2.20E-01	< 1 %	2.34E-01	< 1 %	2.28E+00	1 %	7.06E-01	< 1 %

The values of the 27 impacts defined in the PCR-ed3-EN-2015 04 02 are available in the digital database of pep-ecopassport.org website.

To know the values of the environmental impacts of the products concerned other than the reference product, multiply the values of environmental indicators by the following corresponding factors:

The Reference Product: 0 765 76					
0 765 76: RJ 45 SOCKET C6A STP 2M MOSAIC BL					
with 0 802 51: SUPPORT MOSAIC - WITH SITE PROTECTION FOR 2 MODULES - with 0 788 02L: PLATE MOSAIC - 2 MODULES - WHITE					
Coefficient of extrapolation of environmental indicators					
Associated References	Manufacturing	Distribution	Installation	Use	End of Line
0 765 73 with 0 777 70 with 0 802 51 with 0 788 02L	1	1	1.3	1	1

Registration number: LGRP-01330-V01.01-EN	Drafting rules: «PEP-PCR-ed3-EN-2015 04 02» Supplemented by «PSR-0005-ed2-2016 03 29»
Verifier accreditation N°: VH02	Information and reference documents: www.pep-ecopassport.org
Date of issue: 01-2021	Validity period: 5 years
Independent verification of the declaration and data, in compliance with ISO 14025 : 2010 Internal <input checked="" type="checkbox"/> External <input type="checkbox"/>	
The PCR review was conducted by a panel of experts chaired by Philippe Osset (SOLINNEN)	
PEP are compliant with XP C08-100-1 : 2016 The elements of the present PEP cannot be compared with elements from another program	
Document in compliance with ISO 14025 : 2010: «Environmental labels and declarations. Type III environmental declarations»	
Environmental data in alignment with EN 15804: 2012 + A1 : 2013	

