

LICENCE

No. 19418 replaces No.16165

Issued to:
 Applicant:
Legrand Group Belgium N.V.
Kouterveldstraat 9, Ind. Zone
1831 DIEGEM
Belgium

Licensee:
Legrand Group Belgium N.V.
Kouterveldstraat 9, Ind. Zone
1831 DIEGEM
Belgium



Product : conduit systems for cable management
 Trade name(s) : ARNOULD, LEGRAND
 Type(s)/model(s) : ICTA 3422

The product and any acceptable variation thereto is specified in the annex to this licence and the documents therein referred to.


SGS CEBEC hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard specified in annex
- an inspection of the production location
- a certification agreement with the number 178

SGS CEBEC hereby grants the right to use the CEBEC certification mark


The CEBEC certification mark may be applied to the product as specified in this licence for the duration of the CEBEC certification agreement and under the conditions of the CEBEC certification agreement.

This licence is issued on: 20/03/2015



ir. C. Lana,
 Certification Manager

© Only integral publication of this certificate, including the annex, is allowed
 This certificate is only valid combined with the publication on the following web address: www.sgs.com/ee



SPECIFICATION OF THE CERTIFIED PRODUCT

Product data

Product	:	conduit systems for cable management
Trade name(s)	:	ARNOULD, LEGRAND
Type(s)/Model(s)	:	ICTA 3422
description	:	Conduit system for electrical installation
nominal size(s) (outside diameters)	:	16, 20, 25, 32, 40, 50 & 63 mm
type of conduit	:	non-metallic/corrugated
method of connection	:	non-treadable
resistance to bending	:	pliable/self recovering
flame propagation	:	non flame propagation
colour(s)	:	black, grey anthracite, ivory, grey syrus, blue, brown, green

Additional information

CLASSIFICATION CODING

First digit : 3	Medium compression strength	
Second digit : 4	Heavy impact strength	
Third digit : 2	Minimum permanent application and installation temperature	-5 °C
Fourth digit : 2	Maximum permanent application and installation temperature	90 °C

TESTS

Test requirements

NBN EN 61386-1 based on EN 61386-1:2008
NBN EN 61386-22 based on EN 61386-22:2004 + A11:2010

Test results

The test results are laid down in certification file ref.616388/01

Remarks

This certificate is based on certificate ref. LCIE N° 623870D and test reports ref. 112613-623871D


Conclusion

The examination proved that all test requirements were met.

Checked by, project leader : Zanutto Luigi - 20/03/2015

Department Manager,
Product Certification :

Certification Manager :



Zanutto 2015-03-20

FACTORY LOCATION(S)

Legrand France Lorraine
89, chemin de Montrichard
B.P. 89
54704 PONT A MOUSSON CEDEX
France