



Ref. Certif. No.

FR_716149

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Luminaire for emergency lighting
Self-contained luminaire for emergency lighting

Name and address of the applicant

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the factory

LEGRAND FRANCE.
1 RUE HENRI FREYSSINET
17140 LAGORD
FRANCE

Note: When more than one factory, please report on page 2

☐ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)

legrand

Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

Range B66 LED
6 625 42, 6 625 44

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_701986 dated 15/12/2017. Update further to the evolution of the standard(s)

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60598-1:2014+A1:2017
IEC 60598-2-22:2014+A1:2017

As shown in the Test Report Ref. No. which forms part of this Certificate

173002-766671-A Version : 01


This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 12/01/2023

Signature: Jérôme REYSSON
Certification Officer



ANNEX

Caractéristiques / Characteristics :

Caractéristiques / Characteristics	Valeur / Value
Type / Type	LED M / NM
Tension assignée / Rated voltage	230V
Nature du courant / Nature of supply	~
Fréquence assignée / Rated frequency	50/60 Hz
Puissance assignée / Rated power	6 625 42 : M:2,3W – NM:0,5W 6 625 44 : M:3W – NM:1W
Classe de protection contre les chocs électriques / Class of protection from electric shock	II
Degré IP / IP degree	66
Degré IK / IK degree	08
Flux assigné / Rated lumen output	6 625 42 : 250 lm à 1h 6 625 44 : 450 lm à 1h
Nature accumulateur (Type, Nombre, Tension, Capacité) / Battery type	6 625 42 : Ni-MH [(2 x 1,2 V / 2,2 Ah) + (1 x 1,2 V / 2,2 Ah)] GP GP220SCHT 6 625 44 : Ni-MH [(5 x 1,2 V / 2,2 Ah) + (1 x 1,2 V / 2,2 Ah)] GP GP220SCHT
Lampe de secours (nature, nombre) / Emergency lamp (type, number)	6 Leds



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 12/01/2023

Signature: 

