

CERTIFICATE FI/42475 Issue 2

Our Ref. HEL-CERT210100070-26



Product Range of enclosures

Type CUBO C-series

Trademark ENSTO

Certificate Holder Legrand Finland Oy
Ensio Miettisen katu 2
FI-06100 Porvoo, Finland

Technical information Degree of protection (EN 60529) IP66 / IP67
Mechanical strength (EN 62262) IK08 +35 °C / -25 °C
Static loads mounting plate 2 kg / dm²
Rated voltage 1000 V a.c. / 1500 V d.c.

Other information Empty enclosure for wall mounting
Material: Polycarbonate
Intended location: Outdoor / indoor

The product is certified according to the following standard(s) EN IEC 62208:2023

Validity This certificate is valid until 2031-03-31 provided that the Conditions for FI certification are met. This certificate includes the right to use the FI mark under the condition that changes (if any) will be checked at SGS Fimko before the product is brought onto market and that the conditions for FI certification are met.

Date of issue 2026-03-31

SGS Fimko Oy

Signature


Joonas Leinonen
Certification Manager



Manufacturer

Legrand Finland Oy
Ensio Miettisen katu 2
FI-06100 Porvoo, Finland

Manufacturing site

Legrand Estonia OÜ
Keki 1
EE-76606 Keila, Estonia

Additional information

The series includes the followings types:

Type	size (mm)	Type	size (mm)
CPCF 202013 G/T	200 x 200 x 132	CPCF 202018 G/T	200 x 200 x 187
CPCF 203013 G/T	200 x 300 x 132	CPCF 203018 G/T	200 x 300 x 187
CPCF 204013 G/T	200 x 400 x 132	CPCF 204018 G/T	200 x 400 x 187
CPCF 303013 G/T	300 x 300 x 132	CPCF 303018 G/T	300 x 300 x 187
CPCF 304013 G/T	300 x 400 x 132	CPCF 304018 G/T	300 x 400 x 187
CPCF 306013 G/T	300 x 600 x 132	CPCF 306018 G/T	300 x 600 x 187
CPCF 404013 G/T	400 x 400 x 132	CPCF 404018 G/T	400 x 400 x 187
CPCF 406013 G/T	400 x 600 x 132	CPCF 406018 G/T	400 x 600 x 187

...G grey cover
...T transparent cover

The models CPCF....018 G/T are assembled by adding an extension frame (55 mm) to the CPCF....013 G/T models.

The product has also been subjected to additional glow-wire test at temperature 850 °C besides at the required 650 °C and for determining the electric strength, instead of the test required in IEC 61439-1, a test with voltage 5250 V according to IEC 60439-1 has been performed on the product. The product fulfills these requirements.

This certificate replaces previous certificate no FI/42475 Issue 1, dated 2026-01-28, due to new testing.

As shown in the Test Report(s) No(s): HELES2510000829-1