

MCBs DX³ - 36 kA

thermal magnetic MCBs from 10 A to 80 A - C curve



Performance of DX³ MCBs and auxiliaries **p. 76-77**

Breaking capacity:
36 kA - IEC 60947-2 - 400 V_~
Can be equipped with DX³ auxiliaries and accessories (p. 73-74)

Pack	Cat.Nos	2-pole - 230/400 V _~	
	C curve	Nominal rating In (A)	Number of modules
1	4 100 07	10	3
1	4 100 08	16	3
1	4 100 09	20	3
1	4 100 10	25	3
1	4 100 11	32	3
1	4 100 12	40	3
1	4 100 13	50	3
1	4 100 14	63	3
1	4 100 15	80	3

Pack	Cat.Nos	3-pole - 400 V _~	
	C curve	Nominal rating In (A)	Number of modules
1	4 100 20	10	4.5
1	4 100 21	16	4.5
1	4 100 22	20	4.5
1	4 100 23	25	4.5
1	4 100 24	32	4.5
1	4 100 25	40	4.5
1	4 100 26	50	4.5
1	4 100 27	63	4.5
1	4 100 28	80	4.5

Pack	Cat.Nos	4-pole - 400 V _~	
	C curve	Nominal rating In (A)	Number of modules
1	4 100 33	10	6
1	4 100 34	16	6
1	4 100 35	20	6
1	4 100 36	25	6
1	4 100 37	32	6
1	4 100 38	40	6
1	4 100 39	50	6
1	4 100 40	63	6
1	4 100 41	80	6

MCBs DX³ - 50 kA

thermal magnetic MCBs from 10 A to 63 A - C and D curves



Performance of DX³ MCBs and auxiliaries **p. 76-77**

Breaking capacity:
50 kA - IEC 60947-2 - 400 V_~
Can be equipped with DX³ auxiliaries and accessories (p. 73-74)

Pack	Cat.Nos		Single pole 230/400 V _~	
	C curve	D curve	Nominal rating In (A)	Number of modules
1	4 101 34	4 101 86	10	1.5
1	4 101 35	4 101 87	16	1.5
1	4 101 36	4 101 88	20	1.5
1	4 101 37	4 101 89	25	1.5
1	4 101 38	4 101 90	32	1.5
1	4 101 39	4 101 91	40	1.5
1	4 101 40	4 101 92	50	1.5
1	4 101 41	4 101 93	63	1.5

Pack	Cat.Nos	2-pole - 230/400 V _~	
	C curve	D curve	Number of modules
1	4 101 47	4 101 99	3
1	4 101 48	4 102 00	3
1	4 101 49	4 102 01	3
1	4 101 50	4 102 02	3
1	4 101 51	4 102 03	3
1	4 101 52	4 102 04	3
1	4 101 53		3
1	4 101 54		3

Pack	Cat.Nos	3-pole - 400 V _~	
	C curve	D curve	Number of modules
1	4 101 60	4 102 12	4.5
1	4 101 61	4 102 13	4.5
1	4 101 62	4 102 14	4.5
1	4 101 63	4 102 15	4.5
1	4 101 64	4 102 16	4.5
1	4 101 65	4 102 17	4.5
1	4 101 66	4 102 18	4.5
1	4 101 67	4 102 19	4.5

Pack	Cat.Nos	4-pole - 400 V _~	
	C curve	D curve	Number of modules
1	4 101 73	4 102 25	6
1	4 101 74	4 102 26	6
1	4 101 75	4 102 27	6
1	4 101 76	4 102 28	6
1	4 101 77	4 102 29	6
1	4 101 78	4 102 30	6
1	4 101 79	4 102 31	6
1	4 101 80	4 102 32	6