

## Remote tripping auxiliaries and motorised controls DX<sup>3</sup>



4 062 78



4 062 82



4 062 86



4 062 91



4 062 92

Pack	Cat.Nos	Remote tripping auxiliaries	Number of modules
		<p>To fit on the left-hand side of DX<sup>3</sup> and TX<sup>3</sup> devices                      Maximum 1 remote tripping auxiliary per device                      Allow insertion of the supply busbar                      No tool required for joining together the auxiliary and the main device.                      For MCBs, RCBOs, RCCBs and remote trip isolating switches</p> <p><b>Current shunt trips</b>                      For remote tripping of its associated device via a N/O push button</p>	
1	4 062 76	12 to 48 V $\sim$ / $\equiv$	1
1	4 062 78	110 to 415 V $\sim$	1
		<p><b>Undervoltage releases</b>                      For remote tripping of its associated device in case of mains voltage drop down or with the help of a N/C push button</p>	
1	4 062 80	24 to 48 V $\sim$ / $\equiv$	1
1	4 062 82	230 V $\sim$	1
		<p><b>Power overvoltage protection (POP)</b>                      Protects the circuit by tripping its associated device in case of overvoltage between phase and neutral.                      Tripping threshold : 275 V (eg. in case of neutral interruption)</p>	
1	4 062 86		1
		<p><b>Autonomous shunt trip for N/C push-button</b>                      230 V<math>\sim</math>                      For remote tripping with positive security on a control circuit via a N/C push-button or emergency stop. Does not trigger its associated device in case of mains power failure (the trigger occurs only after a deliberate action of a N/C push-button).                      Supplied with battery                      Minimum working reserve: 60 hours (for remote tripping even if there is no supply voltage)</p>	
1	4 062 83		2

Pack	Cat.Nos	Motorised controls	Number of modules
		<p>For remote control (opening and closing) of their associated device.                      To fit on the left-hand side of DX<sup>3</sup> and TX<sup>3</sup> devices                      For MCBs, RCBOs, RCCBs and remote trip isolating switches (from 1P to 4P)                      Can take one control auxiliary and one signalling auxiliary. No tool required for joining together the motorised control and the main device</p> <p><b>ON/OFF function - for 1 module / pole devices (In up to 63 A)</b></p>	
		Control voltage	Number of modules
1	4 062 90	24-48 V $\sim$ / $\equiv$	1
1	4 062 91	230 V $\sim$	1
		<p><b>ON/OFF function - for 1.5 module / pole devices (In up to 125 A) from 2P to 4P</b></p>	
1	4 062 92	230 V $\sim$	2
		<p><b>ON/OFF + automatic resetting function - for 1 module / pole devices (In up to 63 A)</b>                      Automatically resets the device to which it is associated, thus ensuring continuity of service</p>	
1	4 062 93	24-48 V $\sim$ / $\equiv$	2
1	4 062 95	230 V $\sim$	2