


CERTIFICATE FI/40925

Our Ref. HEL-CERT210100069-01



Product Range of enclosures

Type CUBO D-series (DPCP)

Trademark  or ENSTO

Certificate Holder Ensto Building Systems Finland Oy
Ensio Miettisen katu 2
FI-06150, Porvoo, Finland

Technical information

Degree of protection (EN 60529)	IP66 / IP67
Mechanical strength (EN 62262)	IK08 +35°C / -40 °C
Static loads	mounting plate 2 kg / dm ²
Rated voltage	1000 V a.c. / 1500 V d.c.

Other information Material polycarbonate
Empty enclosure
The series includes following types: See page 3 of this Certificate

The product is certified according to the following standard(s) EN 62208:2011:2011

Validity This certificate is valid until 29 January 2026 provided that the Conditions for FI certification are met. This certificate includes the right to use the FI mark under the condition that changes (if any) will be checked at SGS Fimko before the product is brought onto market and that the conditions for FI certification are met.

Date of issue 29 January 2021

SGS Fimko Ltd

Signature



Seppo Lautamies
Project Manager



Manufacturer

Ensto Building Systems Finland Oy
Ensio Miettisen katu 2
FI-06150, Porvoo, Finland

Manufacturing site

Ensto Building Systems Oü
Keki tn. 1
EE-76606, Keila, Estonia

Directive information

The certified product(s) fulfils requirements of mentioned standard(s) which are harmonised under the Low Voltage Directive (2014/35/EU) at the date of issue of the certificate.

Is based on:

256892-1, 277506-1, 300207-1 and 300793-2

Page 2 of 3

This document is issued by the Company under its General Conditions of Service accessible at http://www.sgs.com/terms_and_conditions.htm. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein.

Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

SGS Fimko Ltd

Takomotie 8, FI-00380 Helsinki, Finland
t. +358 9 696 361 www.sgs.fi

Business ID 0978538-5

Member of the SGS Group (SGS SA)

The serie includes the followings types:

type	size (mm)
DPCP050504 T/G	55 x 53 x 36
DPCP050704 T/G	65 x 53 x 36
DPCP080806 T/G	82 x 80 x 56
DPCP080809 T/G	82 x 80 x 86
DPCP081206 T/G	120 x 80 x 56
DPCP081209 T/G	120 x 80 x 86
DPCP081606 T/G	160 x 80 x 56
DPCP081609 T/G	160 x 80 x 86
DPCP121206 T/G	122 x 120 x 56
DPCP121209 T/G	122 x 120 x 86
DPCP121609 T/G	160 x 120 x 91
DPCP122009 T/G	200 x 120 x 86
DPCP152008 T/G	200 x 150 x 76
DPCP162409 T/G	240 x 160 x 91
DPCP162412 T/G	240 x 160 x 121
DPCP233009 T/G	300 x 230 x 86
DPCP233011 T/G	300 x 230 x 111

Other accessories:

Fastening lug	DFL1
Hinge	DSH11

The product has also been subjected to additional glow-wire test at temperature 850 °C besides at the required 650 °C and for determining the electric strength a test with voltage 5250 V according to IEC 60439-1 has been performed on the product. The product fulfils these requirements.