


Domestic fuse carriers



With label-holders
 With insulated carrier class II, padlockable
 Coupling via supply busbars
 Shielded terminals capacity 2 x 10 mm²
 Possibility to signal indicator blown fuse
 Fuse not supplied

Pack	Cat.Nos	For domestic cylindrical cartridge fuses		
		Conform to EN 60269-1 and IEC 60269-1,3		
		Single pole		
		For domestic cartridges	Cartridge dimensions (mm)	Number of modules
10	0 058 10	10 A - 230 V~	8.5 x 23	1
10	0 058 11	16 A	10.3 x 25.8	1
10	0 058 12	20 A - 400 V~	8.5 x 31.5	1
10	0 058 13	25 A	10.3 x 31.5	1
10	0 058 14	32 A	10.3 x 38	1
		Single pole + neutral		
10	0 058 20	10 A - 230 V~	8.5 x 23	1
10	0 058 21	16 A	10.3 x 25.8	1
10	0 058 22	20 A - 400 V~	8.5 x 31.5	1
10	0 058 23	25 A	10.3 x 31.5	1
10	0 058 24	32 A	10.3 x 38	1

Pack	Cat.Nos	For miniature cylindrical cartridge fuses		
		Conform to EN 60127-6 and IEC 60127-6		
		To protect sensitive equipment: transformers, electronic equipment, etc.		
		Single pole		
		Cartridge dimensions (mm)	Voltage	Number of modules
5	0 058 00	5 x 20	250 V~	1
		Single pole + neutral		
5	0 058 02	5 x 20	250 V~	1

Domestic cartridge fuses



Pack	Cat.Nos		Miniature type 5 x 20					
			Instant reaction fuse - Ceramic body Conform to EN/IEC 60127-2 High rupture capacity (A) For use with dimmers, Viking terminal blocks and emergency lightning units, transformers					
			Rating (Amps)	Voltage ~ (Volts)	Rupture capacity (Amps)	Protected section (mm ²)		Color Indication
10		0 102 02	0.2	250	1500			
10		0 102 05	0.5					
10		0 102 06	0.63					
10		0 102 10	1					
10		0 102 20	2					
10		0 102 30	3.15	250	500			
10		0 102 50	5					
10		0 102 63	6.3					
10		0 102 96 ¹	10					
10		0 102 96 ¹	10					
			Cylindrical					
			6.3 x 23					
			Rating (Amps)	Voltage ~ (Volts)	Rupture capacity (Amps) Copper	Protected section (mm ²)	Color Indication	
10	Without indicator	0 103 06 ²	6	230	6000	1.5		
			8.5 x 23					
10		0 114 06	6	230	6000	1.5	Yellow	
10		0 113 10	10					
			10.3 x 25.8					
10		0 116 10 ²	10	230	6000	2.5	Red	
10		0 116 16 ²	16					
			8.5 x 31.5					
10		0 123 20	20	400	20000	2.5	Green	
			10.3 x 31.5					
10		0 126 16	16	400	20000	4	Blue	
10		0 126 20	20					
10		0 126 25	25					
			10.3 x 38					
10		0 133 32	32	400	20000	6	Brown	
10		0 134 32	32					
			Neutral links					
10		0 123 00	8 x 32 (previously 8.5 x 31.5)					
10		0 133 00	10 x 38					

1: Overrating not described by standards
 2: Conform to BS 1361 (1971)